

TD-Z 551

55" Full-HD Slim Robust LED Backlit Display

TOSHIBA
Leading Innovation >>>



**TAKE VISUAL
IMPACT TO
THE NEXT
DIMENSION.**

Why settle for less when you can enjoy incredible visuals—and big-screen impact—with Toshiba's TD-Z 551 LED Backlit Display. This 55" commercial display offers premium picture quality, thanks to 1080p Full HD resolution and ultrawide 178° viewing angle, plus a slim LED Backlit Display for reproducing high-quality images for a wide range of digital signage and control-room applications.

Built to last, it has a professional and stylish design, featuring a robust metal structure with narrow bezel and slim depth—perfect for continuous 24-hour operation even in the most demanding environments. Infused with famous Toshiba quality and reliability, this commercial HDTV display comes with a three-year limited warranty, for long-term peace of mind.



Portrait mode

Durable Professional Design

Robust structure but narrow bezel and slim depth.

High Resolution

Full HD 1920 x 1080 (1080p) with Toshiba's fine picture settings.

Ultrawide Viewing Angle

178° multi-viewing angle.

OPS (Open Pluggable Standard)

Fully compliant with industry standard OPS supported by Intel® and others.

24/7 Operation

Designed for 24H/7Days Operation* with PID panel and chassis.*

Full Range of Interface

DVI-D, HDMI®, Display Port, D-Sub, BNC, S-Video, Audio Mini Jack, RS232, and USB upstream.

Multiple Orientations

Landscape, portrait and face up mode.

RS-232C/LAN Control Port

Thanks to this display's RS-232C/LAN control port, you can remotely control multiple display's power and input settings simultaneously.

Auto Brightness

Brightness compensation by the ambient light sensors for enhanced visibility and lower power.

3-Year Limited Warranty

Toshiba's commitment to quality and reliability is backed by a three-year limited warranty, so you can enjoy total assurance your display will go the distance.

*Under certain circumstances there is a risk of afterimage effect (burned in images from extended projection), this is not covered in the limited warranty.

TD-Z 551

55" Full-HD Slim Robust LED Backlit Display

TOSHIBA
Leading Innovation >>>

Specifications

Input Voltage

- AC100~240V±10% (50/60Hz)

Power Consumption [W] (Avg.)

- 186

Dimension [mm] (WxHxD)

- 1248 x 719 x 47 (49.1in x 28.3in x 1.8in)

Weight

- NET 62.8 Lbs.

LCD Panel

- 55in PID Exclusive VA Panel

Resolution (H x V)

- 1920 x 1080

Pixel Pitch [mm] (H x V)

- 0.630 x 0.630

Response Time [ms] (Typ.) (G to G)

- 6.5

Luminance [cd/m²] (Typ.)

- 450

Viewing Angle [degree] @ CR>10

- L/R:89; U/D:89

Contrast Ratio (Typ.)

- 4000: 1

PC Frequency Range

- Vertical
 - 50/58.0 - 85Hz (Vertical Analog & Digital)
- Horizontal
 - 15.625/15.734, 31.5 - 91.1KHz (H-Analog) / 31.5 - 91.1KHz (H-Digital)

Input Connector

- DVI-D (with HDCP) x 1
- HDMI® 1.3 x 2
- Displayport 1.1a x 1
- D-SUB (RGB/YPbPr) x 1
- BNC (Composite) x 1
- S-Video x 1
- Audio Mini-Jack x 1
- RS-232 x 1
- USB Upstream x 1

Output Connector


- DVI-D (with HDCP) x 1
- BNC (Composite) x 1
- Audio Mini-Jack x 1
- External Speaker Jack (L/R) x 1
- RS-232 x 1
- USB Downstream x 2"

Features



- DDC/CI
- VESA® Standard
- PIP, POP, Side by Side
- Scheduler
- Portrait Mode
- Face Up Mode

Compliant Regulatory and Guideline

- UL60950-1 / CSA C22.2 No. 60950-1 / EN60950-1 / FCC-A / DOC-A / EN55022-A / EN55024 / EN61000-3-2 / EN61000-3-3 / CE / TUV-S / DenAn(PSE) / VCCI-A / JIS C 61000-3-2 / RoHS / WEEE / J-MOSS / ENERGY STAR® 6.0



- | | |
|------------------------|-------------------------------|
| 1. USB Hub | 8. RS-232 Connector Out |
| 2. DisplayPort In | 9. LAN Connector |
| 3. HDMI® In | 10. S-Video In |
| 4. DVI-D In | 11. Video In |
| 5. DVI-D Out | 12. Video Out |
| 6. D-Sub/YPbPr In | 13. Audio Analog In/Out |
| 7. RS-232 Connector In | 14. External Speaker Terminal |



Back