

40E220U

LCD HDTV

TOSHIBA
Leading Innovation >>>

**STEP UP TO
A BETTER
BRAND OF
BIG SCREEN.**



New High-Value LED with New Aero™ Design

D-LED provides LED picture quality and thin bezel at affordable pricing. The new Aero™ design adds the stylish silver Aero™ wing to create a TV that looks great in any home décor.

1080p Full HD for True Home Theater Quality

Full HD² provides more pixel resolution than standard HD for incredible image clarity.

New Dynamic Picture Mode

Creates pictures that seem to pop off the screen. The new Dynamic Mode enhances color, sharpness, brightness and contrast to provide incredible picture quality.

Audyssey® Audio Technology

Audyssey EQ® provides clear, accurate and natural sound right out of the box. And Audyssey® ABX (Bass Extension) uses sophisticated driver analysis and low-frequency monitoring to extend the range and bass.

Multiple HD Inputs

Full connectivity with two HDMI^{®3} HD Inputs and an HD PC Input, so the TV can also be used as a PC monitor. (Great for PC gaming!)

1080P FULL HD

Top HD picture quality with 1080p Full HD² resolution.

DYNALIGHT 

Dynamic backlight control for deeper blacks and more detail.

HDMI[®] X2

Easily connect to high-definition video and amazingly immersive surround sound in one cable.

PC HIGH DEFINITION INPUT

Easily connect your PC to your TV for the big screen experience.

USB MEDIA 

Easily connect to your favorite tunes and photos, create slideshows, or listen to your personal playlists with this feature.

AUDYSSEY
PREMIUM TELEVISION

For clear, well-balanced sound.

40E220U

SPECIFICATIONS¹

TOSHIBA
Leading Innovation >>>

Screen Size: 40"

- Diagonal Screen Size: 40"

Panel

- Panel Type: CCFL
- Resolution: 1080P Full HD
- Refresh Rate: 60Hz
- Backlight Control: DynaLight®

Video Chassis

- Dynamic Picture Mode
- Native Mode™
- Game Mode

Convenience

- Standard Remote Control

Audio

- Audyssey EQ®
- Audyssey ABX™
- Speaker Output: 14W

Connectivity

- HDMI® with CEC³: 2
- USB Media: 1
- High Definition PC Input: 1
- 3.5mm PC Audio Input: 1
- ColorStream® Component Video: 1
- Composite: 1

Product and Packaging

- VESA Mounting Pattern⁴: 200mm x 200mm
- Limited Warranty: 1 Year Parts & Labor
- Power Consumption (On): 99W
- Power Consumption (Stand-by): 0.2W
- Product Dimensions & Weights
 - Without Stand
 - Dimensions: 38.8"x 23.8"x 3.9"
 - Weight: 28.4 lbs.
 - Packaging
 - Dimensions: 42.1"x 31.1"x 7.4"
 - Weight: 41.8 lbs

- Without Stand

- Dimensions: 38.8"x 23.8"x 3.9"
- Weight: 28.4 lbs.

- Packaging

- Dimensions: 42.1"x 31.1"x 7.4"
- Weight: 41.8 lbs


What's in the box

- Remote Control (CT-90325)
- Batteries (AA x 2)
- Easy Setup Guide
- Quick Start Guide

UPC Code: 022265053805

Country of Origin: Mexico

Remote Control (CT-90325)



Related Products



Single DVD Player



Blu-ray Disc™ Player



Wi-Fi® Built-in Blu-ray Disc™ Player

¹ While every effort has been made at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, system/component/options availability are subject to change without notice. ² 1080p/24 fps encoded content and an HD display capable of accepting a 1080p/24Hz signal required for viewing 1080p/24 fps content. ³ Use of HDMI® w/ CEC requires an HDMI® w/ CEC compatible display/peripheral device. Depending on the specifications of your device, some or all HDMI® w/ CEC functions may not work even if your display/peripheral device is HDMI® w/ CEC compatible. ⁴ If you decide to wall mount your Toshiba television, always use a UL Listed wall bracket appropriate for the size and weight of the television. Care should be taken to place or install the display where it cannot be pushed, pulled over, or knocked down.

© 2012 Toshiba America Information Systems, Inc. ColorStream, DynaLight and Native Mode are registered trademarks or trademarks of Toshiba America Information Systems, Inc. and/or Toshiba Corporation. All other trademarks are the property of their respective owners. All rights reserved.