


Signal Distributor for TRSC1010 | TRLC1050



- 1 signal input port (card type)
- 6 signal output ports (card type)
- Use for TR2010E | TR2006R
- Produce new possibility



Specification

Signal input	2 Multiconnector x 1
Signal output	2 multiconnector x 6
Power input	AC100~240V (50~60Hz)
Power consumption	Max 660W (6 Screens)
Operating temperature	0 ~ 45 ° C
Dimension	Width 482mm
	Height 177mm
	Depth (476mm)