

32L1300U LED HD TV

TOSHIBA

Leading Innovation >>>



FITS IN PERFECTLY, WHEREVER IT GOES.

Not too big, not too small, the Toshiba 32" class L1300U is the perfect sleek, slim and unobtrusive television for use as your primary TV or as an extra TV for your master bedroom. Completely new and elegantly designed with curved corners and a sleek stand, the 32" class L1300U features an energy-efficient LED backlight for bright sharp images and ClearScan® 120Hz technology that doubles the refresh rate for clearer fast motion video. It also features Dynamic Picture Mode for maximum contrast, clarity and color saturation and the versatility of a full set of connections. Beautifully designed and perfectly sized, you can leave it on its stand or mount it anywhere you want a TV that's perfect for any room.

CS120Hz
ClearScan™

ClearScan® 120Hz doubles the refresh rate for clearer fast motion

Dynamic
PICTURE MODE

Dynamic Picture Mode delivers maximum contrast, clarity and color saturation

DYNALIGHT

Dynamic Backlight control for deeper blacks and increased details

LED TV

Energy-efficient LED backlight for vibrant HD picture quality with sharp contrast for lifelike images with natural shadows and highlights

GAME MODE

Game Mode reduces controller delay for faster video gaming action

ColorMaster™

ColorMaster™ for complete six-color management control of hue, saturation and brightness

HDMI X2


High-definition video and digital audio through a single cable

AUDYSSEY
EQ
ABX

Audyssey EQ® and ABX audio technologies for clear, well-balanced sound

USB MEDIA

Easily connect to your favorite tunes and photos, create slideshows, or listen to your personal playlists with this feature



All-new, modern curved corner design in high gloss black with slim neck.



Specifications¹

Screen Size Class: 32"

- Actual Diagonal Screen Size: 31.5"
- Design: High Gloss Black with Slim Neck

Panel

- Panel Type: LED
- Resolution: 720p
- Refresh Rate: ClearScan® 120Hz
- Backlight Control: DynaLight®

Video Chassis

- Dynamic Picture Mode
- ColorMaster™
- Native Mode™
- Game Mode

Convenience

- Remote Control: TV (CEC)

Audio

- Audyssey EQ®
- Audyssey ABX™
- Speaker Output: 14W

Connectivity

- HDMI® with CEC²: 2
- USB Media: 1
- Composite: 1 (shared)
- ColorStream® Component Video: 1

Product and Packaging

- VESA Mounting Pattern⁴: 200m x 200mm
- Limited Warranty: 1 Year Parts & Labor
- Product Dimensions & Weights
 - With Stand
 - Dimensions: 28.9" x 19.3" x 7.1"
 - Weight: 12.8 lbs.
 - Without Stand
 - Dimensions: 28.9" x 17.3" x 3.3"
 - Weight: 11.9 lbs.
- Dimensions: 32.1" x 21.3" x 6.3"
- Weight: 16.8 lbs.
- Power Consumption (On): 33.5W
- Power Consumption (Stand-by): <0.3W
- ENERGY STAR® 6.0 Qualified

What's in the box


- Remote Control (CT-90325)
- Batteries (AAA x 2)
- Resource Guide
- Quick Start Guide
- Warranty

UPC Code: 022265515969

Country of Origin: China



Remote Control
(CT-90325)



Rear Panel Connector Diagram



Side Ports



Rear Panel

Related Products



Symbio™ BD3400 Media Box
and Blu-ray™ Player



Satellite® L855-S5112



SBX4250 Sound Bar

1. While every effort has been made at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, system/component/options availability are subject to change without notice. 2. Use of HDMI® CEC requires an HDMI® CEC compatible display/peripheral device. Depending on the specifications of your device, some or all HDMI® CEC functions may not work even if your display/peripheral device is HDMI® CEC compatible. 3. If you decide to wall mount your Toshiba television, always use a UL Listed wall bracket appropriate for the size and weight of the television. Care should be taken to place or install the display where it cannot be pushed, pulled over, or knocked down.

© 2013 Toshiba America Information Systems, Inc. ClearScan, ColorStream, DynaLight, Native Mode, Satellite and Symbio are registered trademarks or trademarks of Toshiba America Information Systems, Inc. and/or Toshiba Corporation. All other trademarks are the property of their respective owners. All rights reserved.