

32L1400U LED HD TV

TOSHIBA

Leading Innovation >>>



PERFECT MIX OF QUALITY & VALUE.

The Toshiba 32" L1400U is the ideal slim LED TV for your living room or as an extra TV in the bedroom. With a modern design, curved corners and elegant stand, the 32" L1400U is energy efficient, featuring an LED-backlit display. When it comes to image quality, it delivers vibrancy and rich contrast—everything you want from a TV. Equipped with Dynamic Picture Mode, it delivers maximum contrast, clarity and color saturation. Plus, it features DTS TruSurround™ for immersive sound and clear dialog. Beautifully designed and perfectly sized, the 32" L1400U LED HDTV complements any décor whether on its elegant stand or mounted on the wall in your home.



Modern Curved Corner Design
in High-Gloss Black
and Sleek Stand



SLIM LED LED TV SLIM

Energy-efficient LED backlight for vibrant HD picture quality with sharp contrast for lifelike images with natural shadows and highlights

DYNALIGHT

Dynamic Backlight control for deeper blacks and increased details

GAME MODE

Game Mode reduces controller delay for faster video gaming action

ColorMaster™

ColorMaster™ for complete six-color management control of hue, saturation and brightness

Dynamic PICTURE MODE

Dynamic Picture Mode delivers maximum contrast, clarity and color saturation

dts TruSurround

DTS TruSurround™ audio for immersive virtual surround sound

HDTV
HIGH-DEFINITION TELEVISION

Stunning digital picture quality available from High Definition content

HDMI X2

High-definition video and digital audio through a single cable

USB MEDIA

Easily connect to your favorite tunes and photos, create slideshows or listen to your personal playlists



Specifications¹

Screen Size Class: 32"

- Actual Diagonal Screen Size: 31.5"
- Design: Slim Bezel Design & High-Gloss Black

Panel

- Panel Type: Slim LED
- Resolution: 720p
- Refresh Rate: 60Hz
- Backlight Control: DynaLight®

Video Chassis

- Dynamic Picture Mode
- ColorMaster™
- Native Mode™
- Game Mode

Convenience

- Remote Control: TV (CEC)

Audio

- DTS TruSurround™
- Speaker Output: 14W

Connectivity

- HDMI® with CEC³: 2
- USB Media: 1
- Composite: 1 (shared)
- ColorStream® Component Video: 1
- Digital Audio Out: 1

Product and Packaging

- VESA Mounting Pattern⁴: 200mm x 200mm
- Limited Warranty: 1 Year Parts & Labor
- Product Dimensions & Weights
 - With Stand (W x H x D)
 - Dimensions: 28.9" x 19.3" x 7.1"
 - Weight: 13.4 lbs.
 - Without Stand
 - Dimensions: 28.9" x 17.3" x 3.3"
 - Weight: 12.6 lbs.
 - In Packaging
 - Dimensions: 32.1" x 20.9" x 6.3"
 - Weight: 17.0 lbs.

ENERGY STAR® Certified TV

What's in the box


- Remote Control (CT-90325)
- Batteries (AAA x 2)
- Resource Guide
- Quick Start Guide
- Warranty

UPC Code: 022265632017

Country of Origin: China



Remote Control
(CT-90325)



Rear Panel Connector Diagram



Side Port



Rear Panel

Related Products



Symbio™ BD3500 Streaming Media
and Universal Disc Player



Satellite® L55 Series Laptops



SBX4250 Sound Bar

1. While every effort has been made at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, system/component/options availability are subject to change without notice. 2. 1080p/24 fps encoded content and an HD display capable of accepting a 1080p/24Hz signal required for viewing 1080p/24 fps content. 3. Use of HDMI®-CEC requires an HDMI®-CEC compatible display/peripheral device. Depending on the specifications of your device, some or all HDMI®-CEC functions may not work even if your display/peripheral device is HDMI®-CEC compatible. 4. If you decide to wall mount your Toshiba television, always use a UL Listed wall bracket appropriate for the size and weight of the television. Care should be taken to place or install the display where it cannot be pushed, pulled over, or knocked down.

© 2014 Toshiba America Information Systems, Inc. ColorMaster, ColorStream, DynaLight, Native Mode, Satellite and Symbio are registered trademarks or trademarks of Toshiba America Information Systems, Inc. All other trademarks are the property of their respective owners. All rights reserved.