

All information is subject to change without notice. Please read bottom notes.


RoHS compatible

FEATURES : (1) 8.9" W-XGA color display display size for notebook PC
(2) LED Backlight
(3) Transflective

Specification

TENTATIVE

Display size	8.9type(22.6cm)
Number of Pixels	1280(W) X 768(H) (W-XGA)
Display Mode	TFT-LCD (Transflective Type, Normally-White)
Pixel Pitch (mm)	0.1515(W) X 0.1515(H)
Luminance (typ.)	225 cd/m ² at I _{FL} =15mA(rms)
Response Time (max.)	T _{ON} =40ms, T _{OFF} =40ms
Contrast (min.)	140
Viewing Angle (CR≥10)	Vertical : 50 degree, Horizontal : 50 degree
I/F Format & Supply voltage	LVDS RGB 6bit, H/V sync+DE, V _{DD} =3.3V
Operating Temperature	0 to 50 degree C
Outline dimension (mm)	224.0(W) X 133.0(H) X 3.5/5.15max.(D)mm
Weight (approximately)	130g
Backlight	Sidelight (LED)
Power Consumption	3.0W



Rev.0.4R (2009/5/25)

*The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by Toshiba Mobile Display Co., Ltd or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Toshiba Mobile Display Co., Ltd or others.

*The information contained herein may be changed without prior notice. It is therefore advisable to contact Toshiba Mobile Display Co., Ltd before proceeding with the design of equipment incorporating this product.