

32C120U

LCD HDTV

TOSHIBA
Leading Innovation >>>

**OUTSTANDING
PICTURE.
OUTSTANDING
PRICE.**



Quality and Value

The combination of Toshiba quality, new picture and sound technologies, and the right price, makes the C120 series an unbeatable combination of quality and value.

New Dynamic Picture Mode

Creates pictures that seem to pop off the screen. The new Dynamic Mode enhances color, sharpness, brightness and contrast to provide incredible picture quality.

Audyssey® Audio Technology

Audyssey EQ® provides clear, accurate and natural sound right out of the box. And Audyssey® ABX (Bass Extension) uses sophisticated driver analysis and low-frequency monitoring to extend the range and bass.

Multiple HD Inputs

Full connectivity with two HDMI® HD Inputs and an HD PC Input, so the TV can also be used as a large PC monitor. (Great for PC gaming!)



Say goodbye to standard-def with 720p HD resolution



Dynamic Backlight Control for deeper blacks and more detail.



Easily connect to high-definition video and amazingly immersive surround sound in one cable.



Easily connect your PC to your TV for the big screen experience.



Easily connect to your favorite tunes and photos, create slideshows, or listen to your personal playlists with this feature.



For clear, well-balanced sound.

32C120U

SPECIFICATIONS¹

TOSHIBA
Leading Innovation >>>

Screen Size: 32"

- Diagonal Screen Size: 31.5"

Panel

- Panel Type: CCFL
- Resolution: 720P HD
- Refresh Rate: 60Hz
- Backlight Control: DynaLight®

Video Chassis

- Dynamic Picture Mode
- Native Mode™
- Game Mode

Convenience

- Standard Remote Control

Audio

- Audyssey EQ®
- Audyssey ABX™
- Speaker Output: 14W

Connectivity (Jack Pack)

- HDMI® with CEC²: 2 Ports
- USB Media: 1
- High Definition PC Input: 1
- 3.5mm PC Audio Input: 1
- Analog Audio Output: 1
- ColorStream® Component Video: 1
- Composite: 1

Product and Packaging

- VESA Mounting Pattern³: 200mm x 200mm
- Limited Warranty: 1 Year Parts & Labor
- Power Consumption (On): 63W
- Power Consumption (Stand-By): 0.2W
- Product Dimensions & Weights
 - With Stand
 - Dimensions: 31.2"x 21.8"x 9.6"
 - Weight: 19.8 lbs.

- Without Stand

- Dimensions: 31.2"x 19.8"x 3.5"
- Weight: 18.3 lbs.

- Packaging

- Dimensions: 34.5"x 23.1"x 7.4"
- Weight: 28.7 lbs.


What's in the box

- Remote Control (CT-90325)
- Batteries (AA x 2)
- Easy Setup Guide
- Quick Start Guide

UPC Code: 022265053607

Country of Origin: China

Remote Control (CT-90325)



Related Products



Single DVD Player



Blu-ray Disc™ Player



Wi-Fi® Built-in Blu-ray Disc™ Player

1. While every effort has been made at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, system/component/options availability are subject to change without notice. 2. Use of HDMI® w/ CEC requires an HDMI® w/ CEC compatible display/peripheral device. Depending on the specifications of your device, some or all HDMI® w/ CEC functions may not work even if your display/peripheral device is HDMI® w/ CEC compatible. 3. If you decide to wall mount your Toshiba television, always use a UL Listed wall bracket appropriate for the size and weight of the television. Care should be taken to place or install the display where it cannot be pushed, pulled over, or knocked down.

© 2012 Toshiba America Information Systems, Inc. ColorStream, DynaLight and Native Mode are registered trademarks or trademarks of Toshiba America Information Systems, Inc. and/or Toshiba Corporation. All other trademarks are the property of their respective owners. All rights reserved.