

50L1400U LED Full HD TV

TOSHIBA
Leading Innovation >>>



**A VISION
OF QUALITY,
DESIGN & VALUE.**

Extra large and vibrant, the Toshiba 50" L1400U slim LED TV delivers 1080p Full HD and great value in big-screen entertainment. The 50" L1400U stands out with vibrant picture quality and sharp contrast that maintains highlights and shadow details. When it comes to gaming fun, Toshiba's Game Mode gives you that split-second reaction time avid players want most, while Dynamic Picture Mode provides maximum contrast, clarity and color saturation. The 50" L1400U includes DTS TruSurround™ for immersive sound and clear dialog. With a slim, modern, high-gloss black design, the 50" L1400U proves that big can be beautiful.

SLIM LED **LED TV**
SLIM

Energy-efficient LED backlight for vibrant HD picture quality with sharp contrast for lifelike images with natural shadows and highlights

Dynamic
PICTURE MODE

Dynamic Picture Mode delivers maximum contrast, clarity and color saturation

GAME MODE

Game Mode reduces controller delay for faster video gaming action

1080P FULL HD

1080p Full HD resolution—twice the picture detail compared to standard 720p HD

DYNALIGHT

Dynamic Backlight control for deeper blacks and increased details

dts
TruSurround

DTS TruSurround™ audio for immersive virtual surround sound

HDMI X2

High-definition video and digital audio through a single cable

ColorMaster™

ColorMaster™ for complete six-color management control of hue, saturation and brightness

USB MEDIA

Easily connect to your favorite tunes and photos, create slideshows or listen to your personal playlists



Slim, Modern Design
in High-Gloss Black
with Sleek Frame Stand

Specifications¹

Screen Size Class: 50"

- Actual Diagonal Screen Size: 49.5"
- Design: Slim Bezel & High-Gloss Black with Frame Stand

Panel

- Panel Type: Slim LED
- Resolution: 1080p Full HD²
- Refresh Rate: 60Hz
- Backlight Control: DynaLight[®]

Video Chassis

- Dynamic Picture Mode
- ColorMaster[™]
- Native Mode[™]
- Game Mode

Convenience

- Remote Control: TV (CEC)

Audio

- DTS TruSurround[™]
- Speaker Output: 14W

Connectivity

- HDMI[®] with CEC³: 2
- USB Media: 1
- Composite: 1 (shared)
- ColorStream[®] Component Video: 1
- Digital Audio Out: 1

Product and Packaging

- VESA Mounting Pattern⁴: 400mm x 200mm
- Limited Warranty: 1 Year Parts & Labor
- Product Dimensions & Weights
 - With Stand (W x H x D)
 - Dimensions: 44.2" x 27.6" x 8.5"
 - Weight: 35.1 lbs.
 - Without Stand
 - Dimensions: 44.2" x 26.1" x 2.9"
 - Weight: 33.7 lbs.
 - In Packaging
 - Dimensions: 48.7" x 30.1" x 5.9"
 - Weight: 43.4 lbs.

ENERGY STAR[®] Certified TV

What's in the box


- Remote Control (CT-90325)
- Batteries (AAA x 2)
- Resource Guide
- Quick Start Guide
- Warranty

UPC Code: 022265668740

Country of Origin: China [Jan] & Mexico [Feb-]



Remote Control (CT-90325)



Rear Panel Connector Diagram



Side Port



Rear Panel

Related Products



Symbio[™] BDX3500 Streaming Media and Universal Disc Player



Satellite[®] L55 Series Laptops



SBX4250 Sound Bar

1. While every effort has been made at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, system/component/options availability are subject to change without notice. 2. 1080p/24 fps encoded content and an HD display capable of accepting a 1080p/24Hz signal required for viewing 1080p/24 fps content. 3. Use of HDMI[®]-CEC requires an HDMI[®]-CEC compatible display/peripheral device. Depending on the specifications of your device, some or all HDMI[®]-CEC functions may not work even if your display/peripheral device is HDMI[®]-CEC compatible. 4. If you decide to wall mount your Toshiba television, always use a UL Listed wall bracket appropriate for the size and weight of the television. Care should be taken to place or install the display where it cannot be pushed, pulled over, or knocked down.

© 2014 Toshiba America Information Systems, Inc. ColorMaster, ColorStream, DynaLight, Native Mode, Satellite and Symbio are registered trademarks or trademarks of Toshiba America Information Systems, Inc. and/or Toshiba Corporation. All other trademarks are the property of their respective owners. All rights reserved.