

TOSHIBA

TOSHIBA INTERNATIONAL CORPORATION

MINING & MINERALS

SOLUTIONS



**MINING &
MINERALS**

CUSTOMIZED SOLUTIONS FOR COMPLEX DEMANDS

The large installed base of Toshiba International Corporation (TIC) product offerings in the mining and minerals industry demonstrates our customers' confidence in choosing Toshiba. Since many of our products are manufactured under one roof, TIC is able offer customized solutions to meet your application needs. TIC also has the capability to test many of our product offerings together as a complete system before they go out into the field, helping to ensure high levels of quality, performance, and reliability. Customized system solutions include:

- Reliability and Uptime
- Lower Lifecycle Costs and Extended Equipment Life
- Excellent Performance and Efficiency for Reduced Energy Costs
- Superior Product Support for Reduced Maintenance Costs
- Single Source Supplier of Integrated Motor & Drive Systems

LOW VOLTAGE ADJUSTABLE SPEED DRIVES

Toshiba's low voltage adjustable speed drives are used to precisely control a wide variety of applications at various stages in the mining process. Offering some of the highest overload ratings in the industry, these drives provide continual operation for demanding mining applications while maintaining a high level of control. Toshiba's low voltage drives are flexible, reliable, and efficient, making them ideal for pump, fan, compressor, elevator belt, and separator applications.

- **AS3:** 230 V & 460 V; 1/2 HP to 500 HP
- **G9:** 230 V & 460 V; 1 HP to 350 HP
- **PLUS PACK OUTDOOR:** 380 V to 460 V; 60 HP to 1500 HP
- **P9 PUMP DRIVE:** 230 V & 460 V; 3/4 HP to 400 HP

LOW VOLTAGE MOTORS

Toshiba's low voltage motors are designed for harsh mining environments where premium performance, efficiency, and reliability are a must. These low voltage motors have the capability to carry an impressive 20:1 constant torque turn down ratios for 1 to 20 HP, which is critical for operating conveyor mining applications.

- **EQP GLOBAL® SD:** 230/460 V & 575 V; 1/2 HP to 800 HP
- **EQP GLOBAL® 840:** 460 V & 575 V; 3/4 HP to 500 HP
- **EQP GLOBAL® 841:** 460 V & 575 V; 3/4 HP to 500 HP
- **EQP GLOBAL® QUARRY DUTY:** 460 V & 575 V; 5 HP to 600 HP
- **EQP GLOBAL® EXPLOSION PROOF:** 460 V & 575 V; 3/4 HP to 350 HP
- **VERTICAL P-BASE:** 460 V; 3 HP to 350 HP



MEDIUM VOLTAGE ADJUSTABLE SPEED DRIVES

Toshiba's medium voltage adjustable speed drives are some of the most advanced drives on the market. Their multi-level PWM designs allow these drives to have a reduced footprint and component count, helping to lower ownership and maintenance costs. These drives can be retrofitted into mining installations using existing motors while also allowing for multiple-motor operation, which is ideal for operating conveyor mining applications. Their control circuit topology also provides higher performance than competitors' models while using fewer parts for easier maintenance.

- **T300MV2®:** 2400 V, 4160 V & 6600 V; 300 HP to 11,000 HP
- **MTX2® OUTDOOR:** 4160 V; 500 HP to 1500 HP, 3500 HP to 6000 HP
- **MTX® OUTDOOR:** 4160 V; 500 HP to 3000 HP



MEDIUM VOLTAGE MOTORS

Toshiba's medium voltage motors are an excellent choice for tough mining applications where reliability and durability are essential to minimizing down time and maximizing production. Designed and manufactured in Texas and/or Canada, Toshiba's medium voltage motors are constructed with rugged cast iron frames, boosting its high torque/high efficiency performance and unique multi-mount capabilities. High torque motor designs are also solutions for crusher, mill, and conveyor applications.

- **EQP GLOBAL® 587 MV:** 2300/4000 V or 4000 V; 200 HP to 750 HP
- **DURA-BULL TX®:** 2300 V, 4000 V & 6600 V; 100 HP to 1250 HP
- **TEXP:** 2300/4000 V or 6600 V; 200 HP to 1000 HP
- **EQP GLOBAL® 841 MV:** 2300/4000 V or 4000 V; 100 HP to 400 HP
- **TEAAC:** 2300 V, 4000 V & 6600 V; 450 HP to 8000 HP



POWER APPARATUS & COMPONENTS

Toshiba's motor controls are designed to softly start and stop AC motors in fixed speed applications, loads, and extreme conditions, helping to reduce wear and tear on the motors. With one of the highest rated power devices in current-carrying capacity, Toshiba's motor controls are an excellent fit for use with conveyors, compressors, fans, and pumps.

- **TE2 Series Solid State Starter (SSS):** High-end, digitally programmable, reduced voltage heavy-duty starter
- **TE-H Combination & TE-B MLO & Combination Series:** TE2 Series SSS in heavy-duty enclosure, which is ready to work right out-of-the-box
- **JK Series Solid State Starter:** Medium voltage controller; compact design; available in indoor/outdoor enclosure ratings
- **JK Sync-Xfer:** Medium voltage controlgear that is available in multiple configurations, including with multiple motors



TOSHIBA SOLUTIONS

- Research & Development
- Design & Engineering
- Manufacturing
- Sales & Marketing
- Applications Support & Training
- Field Service & Field Service Training
- Customer Service & Project Management
- Logistics & Warehousing

APPLICATIONS

- Pumps
- Fans
- Compressors
- Separators
- Elevator Belts
- Conveyors

APPLICATION SOLUTIONS

PUMPS	BALL, SAG & HPGR MILLS	CRUSHERS	DREDGERS	FANS	COMPRESSORS	SEPARATORS	ROLLERS	SCREENS ROTARY	KILNS	ELEVATOR BELTS	CLASSIFIERS	THICKENERS	FLOTATION CELLS	CONVEYORS
-------	------------------------	----------	----------	------	-------------	------------	---------	----------------	-------	----------------	-------------	------------	-----------------	-----------

LOW VOLTAGE DRIVES

AS3	•		•	•	•	•	•	•	•	•	•	•	•	•
G9	•		•	•	•	•	•	•	•	•	•	•	•	•
Plus Pack Outdoor	•		•	•		•	•	•	•	•	•	•	•	•
P9 Pump Drive	•			•						•				

LOW VOLTAGE MOTORS

EQP Global 840	•	•		•	•	•	•	•	•	•	•	•	•	•
EQP Global 841	•	•		•	•	•	•	•	•	•	•	•	•	•
EQP Global SD	•	•		•		•	•	•	•	•	•	•	•	•
EQP Global Quarry Duty		•	•			•	•	•	•	•				•
EQP Global Explosion Proof	•	•	•		•	•		•	•	•				•
Vertical P-Base	•													

MEDIUM VOLTAGE DRIVES

T300MV2	•	•	•	•	•	•	•	•	•	•	•	•	•	•
MTX2-15	•	•					•		•	•			•	•
MTX2-60	•	•	•		•	•	•		•	•		•	•	•
MTX	•	•		•	•				•	•			•	•

MEDIUM VOLTAGE MOTORS

EQP Global 587 MV	•	•	•	•	•	•	•	•	•	•	•	•	•	•
Dura-Bull TX	•	•	•	•	•	•	•	•	•	•	•	•	•	•
TEXP	•	•	•	•	•	•	•	•	•	•	•	•	•	•
EQP Global 841 MV	•				•	•			•					•
TEAAC	•	•	•	•	•	•	•	•	•	•	•	•	•	•

POWER APPARATUS & COMPONENTS

TE2 Series	•		•	•	•	•	•	•	•	•	•	•	•	•
TE-H & TE-B Series	•		•	•	•	•	•	•	•	•	•	•	•	•
JK Series Solid State Starter	•	•	•	•	•	•	•	•	•	•	•	•	•	•
Sync-Xfer	•	•	•	•	•	•	•	•		•	•		•	•

© 2020
 Toshiba International Corporation
 Motors & Drives
 13131 West Little York Road
 Houston, Texas 77041 USA
 Tel +713-466-0277
 US 1-800-231-1412
 Rev.11ESSENCE1219



TOSHIBA MOTORS & DRIVES
 Adjustable Speed Drives • Motors • Motor Controls



www.toshiba.com/tic