

TD-Z 701

70" Full-HD Slim Robust LED Backlit Display

TOSHIBA
Leading Innovation >>>



**SEE THE BIG
PICTURE—IN
STUNNING HD.**

Whether you need better video conferencing or larger-than-life digital signage, Toshiba's TD-Z 701 LED Backlit Display hits the mark. This versatile 70" commercial display delivers the finest picture quality, thanks to 1080p Full HD resolution and ultrawide 176° viewing angle, for stunning images every time. It's thin and lightweight—yet incredibly durable, too.

Featuring a robust metal structure with narrow bezel and slim depth, it's easy to mount and tough enough for continuous 24-hour operation in virtually any location. Backed by Toshiba's famous quality and reliability, the TD-Z 701 comes with a three-year limited warranty, for maximum peace of mind for years to come.



Portrait mode

Durable Professional Design

Robust structure but narrow bezel and slim depth.

High Resolution

Full HD 1920 x 1080 (1080p) with Toshiba's fine picture settings.

Ultrawide Viewing Angle

176° multi-viewing angle.

OPS (Open Pluggable Standard)

Fully compliant with industry standard OPS supported by Intel® and others.

24/7 Operation

Designed for 24H/7Days Operation* with PID panel and chassis.*

Full Range of Interface

DVI-D, HDMI®, Display Port, D-Sub, BNC, S-Video, Audio Mini Jack, RS232, and USB Upstream.

Multiple Orientations

Landscape, portrait and face up mode.

RS-232C/LAN Control Port

Thanks to this display's RS-232C/LAN control port, you can remotely control multiple display's power and input settings simultaneously.

Auto Brightness

Brightness compensation by the ambient light sensors for enhanced visibility and lower power.

3-Year Limited Warranty

Toshiba's commitment to quality and reliability is backed by a three-year limited warranty, so you can enjoy total assurance your display will go the distance.


*Under certain circumstances there is a risk of afterimage effect (burned in images from extended projection), this is not covered in the limited warranty.

TD-Z 701

70" Full-HD Slim Robust LED Backlit Display

Specifications

<p>Input Voltage</p> <ul style="list-style-type: none"> AC100~240V±10% (50/60Hz) <p>Power Consumption [W] (Avg.)</p> <ul style="list-style-type: none"> 278 <p>Dimension [mm] (WxHxD)</p> <ul style="list-style-type: none"> 1584 x 914 x 66 (62.3in x 35.9in x 2.5in) <p>Weight</p> <ul style="list-style-type: none"> NET 100.9 Lbs. <p>LCD Panel</p> <ul style="list-style-type: none"> 69.5in PID Exclusive VA Panel <p>Resolution (H x V)</p> <ul style="list-style-type: none"> 1920 x 1080 <p>Pixel Pitch [mm] (H x V)</p> <ul style="list-style-type: none"> 0.802 x 0.802 <p>Response Time [ms] (Typ.) (G to G)</p> <ul style="list-style-type: none"> 6 <p>Luminance [cd/m²] (Typ.)</p> <ul style="list-style-type: none"> 500 <p>Viewing Angle [degree] @ CR>10</p>	<ul style="list-style-type: none"> L/R:88; U/D:88 <p>Contrast ratio (Typ.)</p> <ul style="list-style-type: none"> 5000: 1 <p>PC Frequency Range</p> <ul style="list-style-type: none"> Vertical <ul style="list-style-type: none"> 50/58.0 - 85Hz (Vertical Analog & Digital) Horizontal <ul style="list-style-type: none"> 15.625/15.734, 31.5 - 91.1KHz (H-Analog) / 31.5 - 91.1KHz (H-Digital) <p>Input Connector</p> <ul style="list-style-type: none"> DVI-D (with HDCP) x 1 HDMI® 1.3 x 2 Displayport 1.1a x 1 D-SUB (RGB/YPbPr) x 1 BNC (Composite) x 1 S-Video x 1 Audio Mini-Jack x 1 RS-232 x 1 USB Upstream x 1 <p>Output Connector</p> <ul style="list-style-type: none"> DVI-D (with HDCP) x 1 BNC (Composite) x 1 	<ul style="list-style-type: none"> Audio Mini-Jack x 1 External Speaker Jack (L/R) x 1 RS-232 x 1 USB Downstream x 2" <p>Features</p> <ul style="list-style-type: none"> DDC/CI VESA® Standard PIP, POP, Side by Side Scheduler Portrait Mode <p>Compliant Regulatory and Guideline</p> <ul style="list-style-type: none"> UL60950-1 / CSA C22.2 No. 60950-1 / EN60950-1 / FCC-A / DOC-A / EN55022-A / EN55024 / EN61000-3-2 / EN61000-3-3 / CE / TUV-S / DenAn(PSE) / VCCI-A / JIS C 61000-3-2 / RoHS / WEEE / J-MOSS
---	--	--



- | | |
|------------------------|-------------------------------|
| 1. USB Hub | 8. RS-232 Connector Out |
| 2. DisplayPort In | 9. LAN Connector |
| 3. HDMI® In | 10. S-Video In |
| 4. DVI-D In | 11. Video In |
| 5. DVI-D Out | 12. Video Out |
| 6. D-Sub/YPbPr In | 13. Audio Analog In/Out |
| 7. RS-232 Connector In | 14. External Speaker Terminal |

