

TOSHIBA

ADJUSTABLE SPEED DRIVES

Product Offering

LOW & MEDIUM
VOLTAGE
DRIVES



SMART, STRONG DESIGNS WITH PROVEN PERFORMANCE

Toshiba International Corporation (TIC) is proud to be a single-source provider of electric motors, adjustable speed drives, motor control systems, and industrial automation. Known for our quality, performance, and reliability, Toshiba solutions are a preferred choice in demanding applications. With the knowledge and experience to optimize operations and develop a preventive maintenance plan, Toshiba can help reduce maintenance costs and increase uptime. Our in-house capabilities include:

- Research & Development
- Engineering
- Manufacturing
- Technical Sales
- Product & Application Support
- Customer Service
- Project Management
- Field Services & Preventive Maintenance
- Product & Field Service Training

CUSTOMIZABLE SOLUTIONS FOR ADJUSTABLE SPEED DRIVE APPLICATIONS

Toshiba is a leading manufacturer of low and medium voltage adjustable speed drives ranging from 1/2 to 11,000 HP and 230 to 6,900 V. Known for their quality, performance, and reliability, Toshiba drives are a preferred choice in the most demanding applications. With decades of experience, our US-based support team is a knowledgeable partner in providing customer-centric solutions. The large installed base across diverse industries demonstrates customers' confidence in Toshiba drives and service.



INDUSTRIES SERVED

- Agribusiness
- Assembly
- Cement & Aggregate
- Food & Beverage
- Mining & Minerals
- Oil & Gas
- Textiles
- Utilities

APPLICATIONS

- Blowers
- Conveyors
- Crushers
- Fans
- Mixers
- Pumps

ADJUSTABLE SPEED DRIVES



	AS3 General Purpose		AS3 Type 12/IP55		AS3P Outdoor	
Classification	Heavy Duty	Normal Duty	Heavy Duty	Normal Duty	Heavy Duty	Normal Duty
Pulse Input	Standard 6-Pulse Input		Standard 6-Pulse Input		Standard 6-Pulse Input	
240 V Single Phase	N/A		N/A		N/A	
240 V Three-Phase	0.5 to 75 HP	1 to 100 HP	N/A		N/A	
480 V Three-Phase	0.5 to 450 HP	1 to 500 HP	0.5 to 100 HP	1 to 125 HP	7.5 to 450 HP	10 to 500 HP
Ratings 600 to 690 V	2 to 75 HP	3 to 100 HP	N/A		N/A	
Available Enclosures	UL Type 1 (0.5 to 100 HP), Optional NEMA 1 Conduit Box 125 HP & Up	UL Type 1 (1 to 125 HP), Optional NEMA 1 Conduit Box 150 HP & Up	UL Type 12/IP55		UL Type 3R	
Operational Variables/ Operation Control	V/Hz, Slip Compensation, Auto-Torque Boost, Open-Loop Vector, & Closed-Loop Vector, Permanent Magnet Motor Control		V/Hz, Slip Compensation, Auto-Torque Boost, Open-Loop Vector, & Closed-Loop Vector, Pump Control, Permanent Magnet Motor Control		V/Hz, Slip Compensation, Auto-Torque Boost, Open-Loop Vector, & Closed-Loop Vector, Pump Control, Permanent Magnet Motor Control	
Overload Protection	150% for One Minute, 180% for Two Seconds	120% for One Minute, 135% for Two Seconds	150% for One Minute, 180% for Two Seconds	120% for One Minute, 135% for Two Seconds	150% for One Minute, 180% for Two Seconds	120% for One Minute, 135% for Two Seconds
Ambient Rating	-10 to 50°C (60°C with Derate)		-15 to 50°C		-10 to 40°C	
Features	SS Overload Protection, Adjustable Acceleration/ Deceleration, Adjustable Carrier Frequency, Flying Start, Power Ride-Through, Preset Speeds, Pattern Run, Output Frequency 0.01 to 590 Hz, PID Control, Encoder Feedback, My Function Logic Feature & Advanced Pump Control		SS Overload Protection, Adjustable Acceleration/ Deceleration, Adjustable Carrier Frequency, Flying Start, Power Ride-Through, Preset Speeds, Pattern Run, Output Frequency 0.01 to 590 Hz, PID Control, Encoder Feedback, My Function Logic Feature & Advanced Pump Control		SS Overload Protection, Adjustable Acceleration/ Deceleration, Adjustable Carrier Frequency, Flying Start, Power Ride-Through, Preset Speeds, Pattern Run, Output Frequency 0.01 to 590 Hz, PID Control, Encoder Feedback, My Function Logic Feature & Advanced Pump Control	
Communications	Embedded: Dual Port EtherNet/IP®, Modbus TCP, Modbus RTU. Optional: PROFINET®, EtherCAT®, PROFIBUS-DP, DeviceNet®, CAN Open®		Embedded: Dual Port EtherNet/IP®, Modbus TCP, Modbus RTU. Optional: PROFINET®, EtherCAT®, PROFIBUS-DP, DeviceNet®, CAN Open®		Embedded: Dual Port EtherNet/IP®, Modbus TCP, Modbus RTU. Optional: PROFINET®, EtherCAT®, PROFIBUS-DP, DeviceNet®, CAN Open®	
Dynamic Braking	Built-In in 0.5 to 100 HP and 250 HP (External Option in 125 to 200 HP and 300 HP & Up)	Built-In in 1 to 125 HP and 350 HP (External Option in 150 to 250 HP and 400 HP & Up)	Built-In		Built-In	
Software (Available on Website)	ASD Pro		ASD Pro		ASD Pro	

ADJUSTABLE SPEED DRIVES



	S15 Microdrive	NC3 Nanodrive	Plus Pack Outdoor
Classification	Heavy Duty	Heavy Duty	Heavy Duty
Pulse Input	Standard 6-Pulse Input	Standard 6-Pulse Input	6, 12, or 18-Pulse Input
120 V Single Phase	N/A	0.5 to 1 HP	N/A
240 V Single Phase	0.5 to 3 HP	0.5 to 3 HP	N/A
240 V Three-Phase	0.5 to 20 HP	0.5 to 5 HP	N/A
480 V Three-Phase	0.5 to 20 HP	N/A	60 to 1500 HP
Ratings 600 to 690 V	2 to 20 HP	N/A	N/A
Available Enclosures	IP20	IP20	UL Type 1 & 3R
Operational Variables/ Operation Control	V/Hz, Slip Compensation, Auto-Torque Boost, Open-Loop Vector, Automatic Energy Savings for Fans/Pumps & Five-Point V/Hz Custom Curves	V/Hz, Slip Compensation, Auto-Torque Boost, Open-Loop Vector, Automatic Energy Savings for Fans/Pumps & Five-Point V/Hz Custom Curves	*VLP Technology®, V/Hz, Slip Compensation, Auto-Torque Boost, Open-Loop Vector, Constant Torque & Variable Torque
Overload Protection	150% for 60 Seconds; 110% Continuous	150% for 60 Seconds; 100% Continuous	120% for 60 Seconds; 100% Continuous
Ambient Rating	-10 to 50°C (60°C with Derate)	-10 to 50°C (60°C with Derate)	-10 to 50°C
Features	SS Overload Protection, Adjustable Acceleration/Deceleration, Adjustable Carrier Frequency, Flying Start, Power Ride-Through, Preset Speeds, PID Control, Output Frequency 0.5 to 500 Hz, Password Protection for Parameters, Bidirectional PID Control, Logical Operations	SS Overload Protection, Adjustable Acceleration/Deceleration, Adjustable Carrier Frequency, Flying Start, Power Ride-Through, Preset Speeds, PID Control, Output Frequency 0.5 to 500 Hz, Password Protection for Parameters, Bidirectional PID Control, Logical Operations	*VLP Technology®, Automatic Sleep Function, No Flow/Low NPSH Cut-Off, Time-Based Alternation, SS Overload Protection, Adjustable Acceleration/Deceleration, Adjustable Carrier Frequency, Flying Start, Power Ride-Through, Preset Speeds, Pattern Run, Output Frequency 0.01 to 299 Hz, PID Control & My Function Logic Feature
Communications	Embedded: Modbus RTU. Optional: EtherNet/IP®, Modbus TCP, PROFINET®, EtherCAT®, PROFIBUS-DP, DeviceNet®, CAN Open®	Modbus RTU	Optional: Modbus TCP, EtherNet/IP® & TCP/IP®, DeviceNet®, Modbus RTU, Modbus Plus, Profibus DP
Dynamic Braking	Standard	N/A	Optional
Software (Available on Website)	ASD Pro	ASD Pro	ASD Pro

* VLP stands for Virtual Linear Pump

ADJUSTABLE SPEED DRIVES



	T300MV2® (2400 V)	T300MV2® (4160 V)	T300MV2® (6600 V)
Classification	Standard Duty General Purpose	Standard Duty General Purpose	Standard Duty General Purpose
Pulse Input	Standard 24-Pulse Input	Standard 24-Pulse Input	Standard 24-Pulse Input
Ratings	300 to 3,000 HP	300 to 11,000 HP	300 to 9,000 HP
Neutral Point Clamp	Three-Level	Five-Level	Seven-Level
Enclosure	UL Type 1	UL Type 1	UL Type 1
Operational Variables/ Operational Controls	V/Hz, Slip Compensation, Auto-Torque Boost, Sensorless Vector Control, Closed-Loop Vector, Energy savings & Synchronous Transfer	V/Hz, Slip Compensation, Auto-Torque Boost, Sensorless Vector Control, Closed-Loop Vector, Energy savings & Synchronous Transfer	V/Hz, Slip Compensation, Auto-Torque Boost, Sensorless Vector Control, Closed-Loop Vector, Energy savings & Synchronous Transfer
Overload Protection	115% for 60 Seconds Every 10 Minutes; 100% Continuous	115% (1000, 2000, 6000, 8000 HP 110%) for 60 Seconds Every 10 Minutes; 100% Continuous	115% for 60 Seconds Every 10 Minutes; 100% Continuous
Ambient Rating	0 to 40°C (50°C with Derate)	0 to 40°C (50°C with Derate)	0 to 40°C (50°C with Derate)
IEEE® 519 Compliant	Yes	Yes	Yes
Features	Overload Protection, Adjustable Acceleration/ Deceleration, Flying Restart, Power Ride-Through 25% for 5 Cycles, Pattern Run, Output Frequency 0 to 120 Hz, Ground Fault Protection & Internal Input Disconnect	Overload Protection, Adjustable Acceleration/ Deceleration, Flying Restart, Power Ride-Through 25% for 5 Cycles, Pattern Run, Output Frequency 0 to 120 Hz, Ground Fault Protection & Internal Input Disconnect	Overload Protection, Adjustable Acceleration/ Deceleration, Flying Restart, Power Ride-Through 25% for 5 Cycles, Pattern Run, Output Frequency 0 to 120 Hz, Ground Fault Protection & Internal Input Disconnect
Communications	DeviceNet®, Profibus DP, Modbus RTU, Modbus TCP/IP, Tosline, TCNET & EGD	DeviceNet®, Profibus DP, Modbus RTU, Modbus TCP/IP, Tosline, TCNET & EGD	DeviceNet®, Profibus DP, Modbus RTU, Modbus TCP/IP, Tosline, TCNET & EGD
Dynamic Braking	N/A	N/A	N/A
Software (Available on Website)	MVD Tool	MVD Tool	MVD Tool
Software (Available on Website)	MVD Trace Tool (fault data only)	MVD Trace Tool (fault data only)	MVD Trace Tool (fault data only)

ADJUSTABLE SPEED DRIVES



	T300MV2® (6900 V)	T300BMV2 (4160 V)	REGEN DRIVE
Classification	Standard Duty General Purpose	Standard Duty General Purpose	Standard Duty General Purpose
Pulse Input	Standard 24-Pulse Input	Standard 24-Pulse Input	Standard Active Front End
Ratings	7,000 to 10,000 HP	300 to 3,000 HP	700 to 6,000 HP
Neutral Point Clamp	Five-Level	Five-Level	Five-Level
Enclosure	UL Type 1	UL Type 1	UL Type 1
Operational Variables/ Operational Controls	V/Hz, Slip Compensation, Auto-Torque Boost, Sensorless Vector Control, Closed-Loop Vector, Energy savings, & Synchronous Transfer	V/Hz, Slip Compensation, Auto-Torque Boost, Sensorless Vector Control, Closed-Loop Vector & Energy savings	V/Hz, Slip Compensation, Auto-Torque Boost, Sensorless Vector Control, Closed-Loop Vector, Energy savings & Synchronous Transfer
Overload Protection	115% for 60 Seconds Every 20 Minutes; 100% Continuous	115% (1000, 2000HP 110%) for 60 Seconds Every 10 Minutes; 100% Continuous	115% (1000, 2000, 6000 HP 110%) for 60 Seconds Every 10 Minutes; 100% Continuous
Ambient Rating	0 to 40°C (50°C with Derate)	0 to 40°C	0 to 40°C (50°C with Derate)
IEEE® 519 Compliant	Yes	Yes	Yes
Features	Overload Protection, Adjustable Acceleration/Deceleration, Flying Restart, Power Ride-Through 25% for 5 Cycles, Pattern Run, Output Frequency 0 to 120Hz, Ground Fault Protection & Internal Input Disconnect	Overload Protection, Adjustable Acceleration/Deceleration, Flying Restart, Power Ride-Through 25% for 5 Cycles, Pattern Run, Output Frequency 0 to 120 Hz & Ground Fault Protection	Overload Protection, Adjustable Acceleration/Deceleration, Flying Restart, Power Ride-Through 25% for 5 Cycles, Pattern Run, Output Frequency 0 to 120 Hz, Ground Fault Protection & Internal Input Disconnect
Communications	DeviceNet®, PROFIBUS®, Modbus RTU, Modbus TCP/IP, Tosline, TCNET & EGD	DeviceNet®, Profibus DP, Modbus RTU, Modbus TCP/IP, Tosline, TCNET & EGD	DeviceNet®, Profibus DP, Modbus RTU, Modbus TCP/IP & Tosline
Dynamic Braking	N/A	N/A	Yes
Software (Available on Website)	MVD Tool	MVD Tool	MVD Tool
Software (Available on Website)	MVD Trace Tool (fault data only)	MVD Trace Tool (fault data only)	MVD Trace Tool (fault data only)

ADJUSTABLE SPEED DRIVES



	MTX® OUTDOOR	MTX2®-15 OUTDOOR	MTX2®-60 OUTDOOR
Classification	Standard Duty	Standard Duty	Standard Duty
Pulse Input	Standard 36-Pulse Input	Standard 36-Pulse Input	Standard 36-Pulse Input
Ratings	500 to 3,000 HP	500 to 1,500 HP	3,500 to 6,000 HP
Neutral Point Clamp	Five-Level	Five-Level	Five-Level
Enclosure	UL Type 3R	UL Type 3R/4/4X	UL Type 4
Operational Variables/ Operational Controls	V/Hz, Slip Compensation, Auto-Torque Boost, Sensorless Vector Control, Closed-Loop Vector, Energy savings & Synchronous Transfer	V/Hz, Slip Compensation, Auto-Torque Boost, Sensorless Vector Control, Closed-Loop Vector, Energy savings & Synchronous Transfer	V/Hz, Slip Compensation, Auto-Torque Boost, Sensorless Vector Control, Closed-Loop Vector, Energy savings & Synchronous Transfer
Overload Protection	115% for 60 Seconds Every 10 Minutes; 100% Continuous	115% for 60 Seconds Every 10 Minutes; 100% Continuous	115% for 60 Seconds Every 10 Minutes; 100% Continuous
Ambient Rating	-20 to 50°C	-45 to 50°C	-45 to 50°C
IEEE® 519 Compliant	Yes	Yes	Yes
Features	Overload Protection, Adjustable Acceleration/Deceleration, Flying Restart, Power Ride-Through 25% for 5 Cycles, Pattern Run, Output Frequency 0 to 120 Hz, Ground Fault Protection & Internal Input Disconnect	Overload Protection, Adjustable Acceleration/Deceleration, Flying Restart, Power Ride-Through 25% for 5 Cycles, Pattern Run, Output Frequency 0 to 120 Hz, Ground Fault Protection & Internal Input Disconnect	Overload Protection, Adjustable Acceleration/Deceleration, Flying Restart, Power Ride-Through 25% for 5 Cycles, Pattern Run, Output Frequency 0 to 120 Hz, Ground Fault Protection & Internal Input Disconnect
Communications	DeviceNet®, Profibus DP, Modbus RTU, Modbus TCP/IP, Tosline, TCNET & EGD	DeviceNet®, Profibus DP, Modbus RTU, Modbus TCP/IP, Tosline, TCNET & EGD	DeviceNet®, Profibus DP, Modbus RTU, Modbus TCP/IP, Tosline, TCNET & EGD
Dynamic Braking	N/A	N/A	N/A
Software (Available on Website)	MVD Tool	MVD Tool	MVD Tool
Software (Available on Website)	MVD Trace Tool (fault data only)	MVD Trace Tool (fault data only)	MVD Trace Tool (fault data only)

© 2024
Toshiba International Corporation
Motors & Drives Division
13131 West Little York Road
Houston, Texas 77041 USA
Tel +713-466-0277
US 1-800-231-1412
Rev.11ESSENCE1224



Motors • Adjustable Speed Drives • Controls • Industrial Automation

TOSHIBA

www.toshiba.com/tic