







LOW VOLTAGE MOTORS

GENERAL PURPOSE

		<u>i</u>	<u>i</u>	<u></u>					
	Open Drip Proof	Open Drip Proof EPACT	Open Drip Proof EQPIII®	Totally Enclosed Fan Cooled	Totally Enclosed Fan Cooled EPACT	EQPIII®	EQPIII® 840	EQPIII® 841	Expl Proo
EFFICIENCY	HIGH	EPACT	PREMIUM	HIGH	EPACT	PREMIUM	PREMIUM	PREMIUM	PREM
ENCLOSURE	ODP	ODP	ODP	TEFC	TEFC	TEFC	TEFC	TEFC	TEXP
Horsepower	400 to 800 HP	250 to 500 HP	3/4 to 700 HP	1/2 to 800 HP	1 to 500 HP	1/2 to 400 HP	3/4 to 400 HP	3/4 to 200 HP	3/4 to
Speed (60 Hz)	3600, 1800, or 1200 RPM	3600, 1800, or 1200 RPM	3600, 1800, 1200, or 900 RPM	3600, 1800, 1200, or 900 RPM	3600, 1800, 1200, or 900 RPM	3600, 1800, 1200, or 900 RPM	3600, 1800, 1200, or 900 RPM	3600, 1800, 1200, or 900 RPM	3600, 1200, RPM
Voltage (60 Hz)	460 or 575 V	230/460, 460, or 575 V	230/460, 460, or 575 V	230/460, 460, or 575 V	230/460, 460, or 575 V	230/460, 460, or 575 V	460 or 575 V	460 or 575 V	230/46 or 575
Frame Size	449TS through 5810U	445TS through 509U	143T through 509U	56 through 5811U	143T through 5810U	143T through 5810U	143T through 5810U	143T through N449T	143T t N4491
Protection	IP22	IP22	IP22	IP54	IP54	IP54	IP54 or IP56	IP56	IP55
Construction	Cast Iron	Cast Iron	Cast Iron	Cast Iron	Cast Iron	Cast Iron	Cast Iron	Cast Iron	Cast li
Insulation	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class Excee MG1 F (Inverte
Vibration (Unfiltered)	Typically 0.10 IPS or Less	Typically 0.10 IPS or Less	Typically 0.08 IPS or Less; 0.12 IPS or Less Non- NAFTA	Typically 0.10 IPS or Less	Typically 0.10 IPS or Less	Typically 0.08 IPS or Less	Typically 0.06 IPS or Less	Typically 0.04 IPS or Less	Typica IPS or
Area Classification	N/A	N/A	N/A	N/A	N/A	Division 2, Class I, Groups A to D, T3 (200°C), Sine Wave	Division 2, Class I, Groups A to D, T3 (200°C), Sine Wave	Division 2, Class I, Groups A to D, T3 (200°C), Sine Wave	Divisio Class D & C Group T3B (1 Sine V
Warranty (From Date of Manufacture)	24 Months	24 Months	36 Months	24 Months	24 Months	36 Months	36 Months	60 Months	36 Mo

DEFINITE PURPOSE



osion f	Global® SD	Global® 840	Global® 841	Oil Well Pump	Dry Kiln	Brake	Design C	Quarry Duty	Vector Ready	ן נ
UM	PREMIUM	PREMIUM	PREMIUM	HIGH	HIGH	PREMIUM	EPACT	HIGH	PREMIUM	P
	TEFC	TEFC	TEFC	ODP	ODP	TEFC	TEFC	TEFC	TEFC, TENV, TEBC	Т
350 HP	3/4 to 700 HP	3/4 to 500 HP	3/4 to 300 HP	5 to 100 HP	3 to 25 HP	1/2 to 30 HP	1 to 200 HP	125 to 600 HP	1 to 350 HP	1
1800, or 900	3600, 1800, or 1200 RPM; 3000, 1500, or 1000 RPM (50 Hz)	3600, 1800, or 1200 RPM; 3000, 1500, or 1000 RPM (50 Hz)	3600, 1800, or 1200 RPM	1200 RPM	1800, 1200, or 900 RPM	1800, 1200, or 900 RPM	1800 or 1200 RPM	1800, 1200, or 900 RPM	1800 or 1200 RPM	1 F
60, 460, V	230/460, 460, or 575 V; 190/380 or 380 V (50 Hz)	460 or 575 V; 380 V (50 Hz)	460 or 575 V	230/460/796 V	460 V (575 V Available Upon Request)	230/460, 460, or 575 V	230/460, 460, or 575 V	460 or 575 V	460 V (575 V Available Upon Request)	4
hrough	143T through 5810U	143T through 5810U	143T through N449T	215T through 444T	184T through 365T	143T through 286T	143T through 449T	505U through 5810U	143T through N449T	5 2
	IP54	IP54 or IP56	IP56	IP22	IP22	IP23 or 1P54	IP44 or IP54	IP54	IP54	11
on	Cast Iron	Cast Iron	Cast Iron	Cast Iron	Cast Iron	Cast Iron	Cast Iron	Cast Iron	Cast Iron	3 5 5
F, ds NEMA Part 31 <i>r Duty)</i>	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class F, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class H, Exceeds NEMA MG1 Part 31 (Inverter Duty)	Class F, Exceeds NEMA MG1 Part 31 Definite Purpose (Inverter Duty)	С Е (/			
lly 0.08 Less	Typically 0.08 IPS or Less	Typically 0.06 IPS or Less	Typically 0.04 IPS or Less	Typically 0.12 IPS or Less	Typically 0.10 IPS or Less	T				
n 1, I, Group ass II, s E to G, 65°C), <i>I</i> ave	Division 2, Class I, Groups A to D, T3 (200°C), Sine Wave	Division 2, Class I, Groups A to D, T3 (200°C), Sine Wave	Division 2, Class I, Groups A to D, T3 (200°C), Sine Wave	N/A	N/A	N/A	N/A	N/A	N/A	N
nths	36 Months	36 Months	60 Months	24 Months	12 or 18 Months	36 Months	24 Months	24 Months	36 Months	3

MEDIUM VOLTAGE MOTORS

















ONE CALL. ONE SOLUTION.

Toshiba International Corporation is proud to be a single-source solution for our customers, offering a complete product lineup of electric motors, adjustable speed drives, and motor starters for a variety of applications. Many of these products are manufactured at our one million square foot manufacturing facility located in Houston, Texas. Our Houston facility has extensive knowledge and experience, offering the following services in-house:

- Research & Development
- Design & Engineering
- Manufacturing
- Sales & Marketing

- Applications Support
- Field Service
- Customer Service & Project Management
- Logistics & Warehousing
- Product Application & Field Service Training

> ONE STOP FOR ALL YOUR MOTOR NEEDS

Toshiba is a leading manufacturer of low voltage motors from ½ to 800 HP and 230 to 575 V and medium voltage motors from 100 to 50,000 HP and 2,300 to 13,800 V. Our extensive motor product offering and large installed base in the numerous industries demonstrates our customers' confidence in choosing Toshiba motors. Since many of our products are manufactured under one roof, we can offer customized solutions to meet your application needs. We also have the capability to test our products together, as a complete system, before it goes out into the field—ensuring the highest level of quality, performance, and reliability.

> APPLICATIONS



Oil & Gas



Mining & Minerals





Aggregate





Food & Beverage



Utilities





Textiles

Agribusiness

TOSHIBA INDUSTRIAL PRODUCTS:

- Motors
- Adjustable Speed Drives
- Motor Controls
- Instrumentation & PLCs
- Uninterruptible Power Systems





www.toshiba.com/motors

© 2013 Toshiba International Corporation • Industrial Division • 13131 West Little York Road • Houston, Texas 77041 USA • Tel +713-466-0277 US 1-800-231-1412 • Rev. 130614