


				Issued Date	12/18/20)19	Transmit #	
		_		Issued By	dschoe	ck	Issued Rev	
	SHIE	TYF	PICAL MOTO	R PERFORM	ANCE DATA	N .		
Model:	0054SDSR42/	4-Ρ						
HP	kW	Pole	FL RPM	Frame	Voltage	Hz	Phase	FL Amps
5	3.7	4	1750	184TC	230/460	60 NEMA	3	13.0/6.5 Ambient
Enclosure	IP	Ins. Class	S.F.	Duty	Nom. Eff.	Design	kVA Code	(°C)
TEFC	55	F	1.15	CONT	89.5	В	J	40 C
.oad	HP	kW	Amp		Efficiency	/ (%)	Power Fa	
Full Load	5	3.7	6.		89.7		81	
4 Load	3.75	2.8	5.	-	89.3		77	
/2 Load	2.50 1.25	1.9 0.9	4.	-	87.6 81.7		69 51	
∕₄ Load No Load	1.20	0.8	2.		01.7		51	
load Locked Rotor							5. 52	
			Torqu	e				Rotor w
Full Lo	bad	Locke	d Rotor	Pul	Up	Brea	ak Down	Inertia
(lb-f			FLT)	(% F	•		6 FLT)	(lb-ft²)
15	-	-	, 55	24	-	-	370	0.50
Safe Stall		Sound Pressure		Bearing	s*		Approx. Mo	otor Weight
Safe Stall Cold 35	Time(s) Hot 15	Sound Pressure dB(A) @ 1M	D 63062	E	s* NDE 6306ZZ		Approx. Mc (Ib 11	s)
Cold 35 Bearings are the only re Motor Options: Product Family:EQI	Hot 15 ecommended spar	Pressure dB(A) @ 1M - e part(s).		E	NDE		(Ib	s)
Cold 35 Bearings are the only re Notor Options: Product Family:EQI Mounting:C-Face F Mounting:C-Face F Sustomer Sustomer PO Sales Order	Hot 15 ecommended spar	Pressure dB(A) @ 1M - e part(s).		E	NDE		(Ib	s)
Cold 35 Bearings are the only re Product Family:EQI Mounting:C-Face F Customer Customer PO Sales Order Project # Tag:	Hot 15 ecommended spar P Global SD CF ooted,Shaft:T S	Pressure dB(A) @ 1M - e part(s). Face Footed shaft		E	NDE		(Ib	s)
Cold 35 Bearings are the only re Motor Options: Product Family:EQI Mounting:C-Face F Mounting:C-Face F Customer Customer PO Sales Order Project # Tag:	Hot 15 ecommended spar P Global SD CF ooted,Shaft:T S	Pressure dB(A) @ 1M - e part(s). Face Footed thaft	63062	E ZZC3	NDE 6306ZZ	C3	(Ib	s)
Cold 35 Bearings are the only re Motor Options: Product Family:EQI Mounting:C-Face F Mounting:C-Face F Customer Customer PO Sales Order Project #	Hot 15 ecommended spar P Global SD CF ooted,Shaft:T S	Pressure dB(A) @ 1M - e part(s). Face Footed shaft	63062	E ZZC3	NDE 6306ZZ	C3	(Ib	s)

				Issued Date	12/18/20)19	Transmit #	
		_		Issued By	dschoe	ck	Issued Rev	
TOS	SLIE							·
		ТУС		R PERFORM				
					ANCE DATA	•		
Model:	0054SDSR42/	λ-P						
HP	kW	Pole	FL RPM	Frame	Voltage	Hz	Phase	FL Amps
5	3.7	4	1430	184TC	190/380	50	3	16.6/8.3
Enclosure	IP	Ins. Class	S.F.	Duty	NEMA Nom. Eff.	NEMA Design	kVA Code	Ambient (°C)
TEFC	55	F	1.0	CONT	86.5	B	Н	40 C
Load	HP	kW	Amp	eres	Efficiency	/ (%)	Power Fa	actor (%)
Full Load	5	3.7	8.		86.4		79	
¾ Load	3.75	2.8	6.	5	87.7		74	.6
½ Load	2.50	1.9	5.	0	87.1		64	.7
¼ Load	1.25	0.9	4.	0	81.1		43	.3
No Load			3.				6.	
Locked Rotor			52	.9			63	.2
			Torqu	e				Rotor wk ²
Full Lo	ad		d Rotor	Pull			ak Down	Inertia
(lb-ft)	(%	FLT)	(% F	FLT)	(%	% FLT)	(lb-ft²)
18.4		22	20	20			280	0.43
Sato Stall I		Pressure						
Safe Stall T Cold	Hot	Pressure		Bearing				otor Weight
Cold	Hot	Pressure dB(A) @ 1M	D	E	NDE	22	(Ib	os)
		Pressure	DI 63062	E		C3	(Ib	
Cold	Hot 15 commended spare	Pressure dB(A) @ 1M		E	NDE	C3	(Ib	os)
Cold 35 Bearings are the only re Motor Options: Product Family:EQP Mounting:C-Face Fo	Hot 15 commended spare	Pressure dB(A) @ 1M		E	NDE	C3	(Ib	os)
Cold 35 Bearings are the only re- Motor Options: Product Family:EQP Mounting:C-Face Fo	Hot 15 commended spare	Pressure dB(A) @ 1M		E	NDE	C3	(Ib	os)
Cold 35 Bearings are the only re Motor Options: Product Family:EQP Mounting:C-Face Fo Mounting:C-Face Fo	Hot 15 commended spare	Pressure dB(A) @ 1M		E	NDE	C3	(Ib	os)
Cold 35 Bearings are the only re Motor Options: Product Family:EQP Mounting:C-Face Fo Mounting:C-Face Fo Customer Customer PO Sales Order	Hot 15 commended spare	Pressure dB(A) @ 1M		E	NDE	C3	(Ib	os)
Cold 35 Bearings are the only re- Motor Options: Product Family:EQP Mounting:C-Face Fo Mounting:C-Face Fo Sales Order Project #	Hot 15 commended spare	Pressure dB(A) @ 1M		E	NDE	C3	(Ib	os)
Cold 35 Bearings are the only re- Motor Options: Product Family:EQP Mounting:C-Face Fo Mounting:C-Face Fo Sales Order Project # Tag:	Hot 15 commended spare P Global SD CF poted,Shaft:T S	Pressure dB(A) @ 1M - e part(s). ace Footed haft		E	NDE	C3	(Ib	os)
Cold 35 Bearings are the only re- Motor Options: Product Family:EQP Mounting:C-Face Fo Mounting:C-Face Fo Sales Order Project # Tag:	Hot 15 commended spare P Global SD CF poted,Shaft:T S	Pressure dB(A) @ 1M - e part(s). ace Footed haft	63062	E ZZC3	NDE 6306ZZ		(Ib	os)
Cold 35 Bearings are the only re Motor Options: Product Family:EQP Mounting:C-Face Fo	Hot 15 commended spare 2 Global SD CF boted,Shaft:T S	Pressure dB(A) @ 1M - e part(s). ace Footed haft	63062	E	NDE 6306ZZ	AS U.S.A.	(Ib	DS) 16


				Issued Date	12/18/20	019	Transmit #	
		_		Issued By	dschoe	ck	Issued Rev	
TUS	SHIB	A SI	PEED TORQ	UE/CURREN	T CURVE			
Model:	0054SDSR42A-I	Ρ						
HP	kW	Pole	FL RPM	Frame	Voltage	Hz	Phase	FL Amps
5	3.7	4	1750	184TC	230/460	60	3	13.0/6.5
Enclosure	IP	Ins. Class	S.F.	Duty	NEMA Nom. Eff.	NEMA Design	kVA Code	Ambient (°C)
TEFC	55	F	1.15	CONT	89.5	В	J	40 C
	Rotor wk ²				Torque			
Locked Rotor Amps	Inertia (Ib-ft²)	Full Load (lb-ft)	Locked (%		Pull Up (%)		Break Down (%)	
	0.50	15	255		240		370	



Design Values

All characteristics are average expected values.								
	TOSHIBA INTERNATIONAL CORPORATION · HOUSTON, TEXAS U.S.A.							
Engineering	zxie	Doc. Written By	D. Suarez	Doc.# / Rev	MPCF-1121/1			
Engr. Date	7/19/2019	Doc. Approved By	M. Campbell	Doc. Issued	9/20/2019			

				Issued Date	12/18/20	019	Transmit #	
		_		Issued By	dschoe	eck	Issued Rev	
TOS	SHIB	A Si	PEED TORQ	UE/CURREN	T CURVE			
Model:	0054SDSR42A-F	D						
HP	kW	Pole	FL RPM	Frame	Voltage	Hz	Phase	FL Amps
5	3.7	4	1430	184TC	190/380	50	3	16.6/8.3
Enclosure	IP	Ins. Class	S.F.	Duty	NEMA Nom. Eff.	NEMA Design	kVA Code	Ambient (°C)
TEFC	55	F	1.0	CONT	86.5	В	Н	40 C
	Rotor wk ²	•		•	Torque	•		
Locked Rotor	Inertia	Full Load	Locked	Rotor	Pull Up		Break Down	
Amps	(lb-ft²)	(lb-ft)	(%	6)	(%)	(%))
	0.43	18.4	220		200		280	



Design Values

All characteristics are average expected values.									
	TOSHIBA INTERNATIONAL CORPORATION · HOUSTON, TEXAS U.S.A.								
Engineering	garce	Doc. Written By	D. Suarez	Doc.# / Rev	MPCF-1121/1				
Engr. Date	6/5/2015	Doc. Approved By	M. Campbell	Doc. Issued	9/20/2019				

