

UNITS: INCHES

ROTATION FROM NDE

|   |                             |
|---|-----------------------------|
|   |                             |
| <input checked="" type="checkbox"/> CCW | <input type="checkbox"/> CW |

NOTES:  
 1. MAIN CONDUIT BOX MAY BE ROTATED IN 90° INCREMENTS  
 2. STANDARD PRODUCT USES BI-DIRECTIONAL FAN. OPPOSITE ROTATION AVAILABLE ONLY BY CONNECTION CHANGE.  
 3. KEY DIMENSIONS EQUAL 0.500"x 0.500"x 2.00" (MOTOR SUPPLIED WITH KEY)

TOSHIBA RESERVES THE RIGHT TO MAKE CHANGES OF TECHNICAL IMPROVEMENT AND THE DATA MAY CHANGE WITHOUT NOTICE  PRELIMINARY

DO NOT USE FOR CONSTRUCTION, INSTALLATION, OR APPLICATION PURPOSES UNLESS THE DRAWING IS MARKED AS CERTIFIED  CERTIFIED

**TOSHIBA**  
 www.toshiba.com/tic  
 TOSHIBA INTERNATIONAL CORPORATION

TOTALLY ENCLOSED FAN COOLED  
 ROUND BODY C-FACED  
 3 PHASE INDUCTION MOTOR  
 324TSC-326TSC F1 ASSEMBLY

DRAWING #: MDSL286-06  
 REV. DATE: 07/11/18 REV. #: 2 PER.: M. O'DOWD  
 REV. DESCRIP.:



|             |           |            |  |
|-------------|-----------|------------|--|
| Issued Date | 9/24/2019 | Transmit # |  |
| Issued By   | dschoeck  | Issued Rev |  |

### TYPICAL MOTOR PERFORMANCE DATA

Model: 0502XDSC44B-P

| HP        | kW | Pole       | FL RPM | Frame  | Voltage        | Hz          | Phase    | FL Amps      |
|-----------|----|------------|--------|--------|----------------|-------------|----------|--------------|
| 50        | 37 | 2          | 3540   | 326TSC | 575            | 60          | 3        | 46           |
| Enclosure | IP | Ins. Class | S.F.   | Duty   | NEMA Nom. Eff. | NEMA Design | kVA Code | Ambient (°C) |
| TEFC      | 56 | F          | 1.15   | CONT   | 93             | B           | G        | 40 C         |

| Load         | HP    | kW   | Amperes | Efficiency (%) | Power Factor (%) |
|--------------|-------|------|---------|----------------|------------------|
| Full Load    | 50    | 37.3 | 46.0    | 93.0           | 87.6             |
| ¾ Load       | 37.50 | 28.0 | 35.2    | 92.3           | 85.8             |
| ½ Load       | 25.00 | 18.6 | 25.5    | 90.3           | 80.6             |
| ¼ Load       | 12.50 | 9.3  | 17.4    | 84.9           | 63.4             |
| No Load      |       |      | 12.2    |                | 6.7              |
| Locked Rotor |       |      | 290     |                | 43.6             |

| Torque            |                      |                 |                    | Rotor wk <sup>2</sup> Inertia (lb-ft <sup>2</sup> ) |
|-------------------|----------------------|-----------------|--------------------|---|
| Full Load (lb-ft) | Locked Rotor (% FLT) | Pull Up (% FLT) | Break Down (% FLT) |   |
| 74.2              | 270                  | 235             | 280                | 6.39  |

| Safe Stall Time(s) |     | Sound Pressure dB(A) @ 1M | Bearings* |        | Approx. Motor Weight (lbs) |
|--------------------|-----|---------------------------|-----------|--------|----------------------------|
| Cold               | Hot |                           | DE        | NDE    |                            |
| 35                 | 15  | -                         | 6312C3    | 6312C3 | 0                          |

\*Bearings are the only recommended spare part(s).

**Motor Options:**  
Mounting:C-Face Round,Shaft:TS Shaft

|             |  |
|-------------|--|
| Customer    |  |
| Customer PO |  |
| Sales Order |  |
| Project #   |  |

Tag:

All characteristics are average expected values.

**TOSHIBA INTERNATIONAL CORPORATION · HOUSTON, TEXAS U.S.A.**

|             |           |                  |             |             |               |
|-------------|-----------|------------------|-------------|-------------|---------------|
| Engineering | garce     | Doc. Written By  | D. Suarez   | Doc.# / Rev | MPCF-1119 / 1 |
| Engr. Date  | 8/21/2015 | Doc. Approved By | M. Campbell | Doc. Issued | 9/20/2019     |




|             |           |            |  |
|-------------|-----------|------------|--|
| Issued Date | 9/24/2019 | Transmit # |  |
| Issued By   | dschoeck  | Issued Rev |  |

### SPEED TORQUE/CURRENT CURVE

Model: 0502XDSC44B-P

|                   |   |                   |                  |        |                |             |                |              |
|-------------------|---|-------------------|------------------|--------|----------------|-------------|----------------|--------------|
| HP                | kW  | Pole              | FL RPM           | Frame  | Voltage        | Hz          | Phase          | FL Amps      |
| 50                | 37  | 2                 | 3540             | 326TSC | 575            | 60          | 3              | 46           |
| Enclosure         | IP  | Ins. Class        | S.F.             | Duty   | NEMA Nom. Eff. | NEMA Design | kVA Code       | Ambient (°C) |
| TEFC              | 56  | F                 | 1.15             | CONT   | 93             | B           | G              | 40 C         |
| Locked Rotor Amps | Rotor wk <sup>2</sup> Inertia (lb-ft <sup>2</sup> ) | Torque            |                  |        |                | Pull Up (%) | Break Down (%) |              |
|                   |   | Full Load (lb-ft) | Locked Rotor (%) |        |                |             |                |              |
| 290               | 6.39  | 74.2              | 270              |        | 235            | 280         |                |              |

### Design Values



|             |  |  |     |
|-------------|--|--|-----|
| Customer    |  | wk <sup>2</sup> Load Inertia (lb-ft <sup>2</sup> ) | -   |
| Customer PO |  | Load Type  | -   |
| Sales Order |  | Voltage (%)  | 100 |
| Project #   |  | Accel. Time  | -   |

Tag:

All characteristics are average expected values.

#### TOSHIBA INTERNATIONAL CORPORATION · HOUSTON, TEXAS U.S.A.

|             |           |                  |             |             |             |
|-------------|-----------|------------------|-------------|-------------|-------------|
| Engineering | garce     | Doc. Written By  | D. Suarez   | Doc.# / Rev | MPCF-1121/1 |
| Engr. Date  | 8/21/2015 | Doc. Approved By | M. Campbell | Doc. Issued | 9/20/2019   |

### Motor Connection Diagram 3 Leads - Delta Connection



Switch L1 and L2 to reverse rotation

Each lead may consist of more than one cable.  
If multiple cables represent a single lead, each one  
of them will be labeled with the appropriate lead number.