



FRAME SIZE	MOUNTING				CONDUIT BOX						
	E	2F	H	BA	AA	AB	AC	AE	AF	XL	XN
324T/TS	6.25	10.50	0.66	5.25	2.5 3.0	14.09	11.61	10.95	5.51	--	--
326T/TS	6.25	12.00	0.66	5.25	2.5 3.0	14.09	11.61	10.95	5.51	--	--

FRAME SIZE	MOTOR DIMENSIONS										
	A	B	C	D	G	J	K	M	O	T	P
324T	14.88	12.68	26.26	8.00	0.91	3.15	3.15	--	16.46	2.70	16.69
324TS	14.88	12.68	24.76	8.00	0.91	3.15	3.15	--	16.46	2.70	16.69
326T	14.88	14.17	27.76	8.00	0.91	3.15	3.15	--	16.46	2.70	16.69
326TS	14.88	14.17	26.26	8.00	0.91	3.15	3.15	--	16.46	2.70	16.69

FRAME SIZE	SHAFT EXTENSION			KEY SEAT			BEARINGS		MAXIMUM WEIGHT
	N-W	V	U	R	S	ES	LS	OS	
324T	5.25	5.00	2.125	1.845	0.500	3.875	6312	6212ZZ	516 lbs.
324TS	3.75	3.50	1.875	1.591	0.500	2.000	6312C3	6212ZZ	512 lbs.
326T	5.25	5.00	2.125	1.845	0.500	3.875	6312	6212ZZ	560 lbs.
326TS	3.75	3.50	1.875	1.591	0.500	2.000	6312C3	6212ZZ	565 lbs.

ALL DATA SUBJECT TO CHANGE WITHOUT NOTICE.  
FOR CONSTRUCTION USE ONLY CERTIFIED DATA.

- NOTES:
- DIMENSION V REPRESENTS LENGTH OF STRAIGHT PART OF SHAFT.
  - CONDUIT BOX MAY BE ROTATED IN 90° INCREMENTS AND MAY BE MOUNTED ON OPPOSITE SIDE ON SPECIAL ORDER.
  - T KEY DIMENSIONS EQUAL S x S x 3.88  
TS KEY DIMENSIONS EQUAL S x S x 2.00 (MOTOR SUPPLIED WITH KEY)
  - MOTOR WEIGHT SHOWN IS MAXIMUM HORSEPOWER IN FRAME.

CERTIFIED DATA

CUSTOMER: \_\_\_\_\_ P.O. NO.: \_\_\_\_\_ TAG NO.: \_\_\_\_\_  
 MOTOR MODEL NO.: 0602DPSC31B-P TOSHIBA FILE NO.: \_\_\_\_\_  
 HP: 60 RPM (SYN.): 3600 VOLTAGE: 575 Hz: 60  
 FRAME SIZE: 326TS LOG NO.: \_\_\_\_\_ LOG REV. LEVEL: \_\_\_\_\_  
 REMARKS: \_\_\_\_\_

PER: \_\_\_\_\_ ISSUE DATE: \_\_\_\_\_ SUPERSEDES: \_\_\_\_\_

**TOSHIBA INTERNATIONAL CORPORATION**  
**Industrial Division / Houston Motor Plant**

**SQUIRREL CAGE INDUCTION MOTOR  
 PERFORMANCE SPECIFICATIONS**

INDEX	MPCF-1033
SHEET NO.	1 of 1
ISSUED	11/08/96
SUPERSEDES	10/06/95
REVISION	1
WRITTEN BY	R. EVANS
APPROVED BY	<i>Jay Bugbee</i>

Customer Tag:

CUSTOMER:  
 TIC SR No.:  
 Customer PO:

**MOTOR NAMEPLATE DATA**

H.P.: 60	VOLTS: 575	3 Ø / 60	Hz	S. RPM: 3600
FRAME: 326TS	ENCL: ODP	FLAMPS: 54.4		FLRPM: 3535
FORM: VCK1	S.F.: 1.15	NEMA DESIGN: B		INSUL CLASS: F
TYPE: TIKK	AMB.: 40C	CODE: E		DUTY: CONT.
MODEL No.: 0602DPSC31B-P		kW: 45		Serial No.:
NOM. EFF.: 93.6	MIN. EFF.:	P.F.: 88.5		

<b>AMPERAGE</b> Locked Rotor: 272	<b>TORQUES</b> FULL LOAD (lb-ft.): 89.1 LOCKED ROTOR (%): 160 BREAK DOWN (%): 200	<b>** BEARINGS:</b> Drive End: 6312C3 Opposite Drive End: 6212C3
--------------------------------------	--	--

<b>EFFICIENCY (%)</b> FULL LOAD: 93.6 3/4 LOAD: 93.7 1/2 LOAD: 93.1	<b>POWER FACTOR (%)</b> FULL LOAD: 88.5 3/4 LOAD: 85 1/2 LOAD: 80.5
--	--

ALL CHARACTERISTICS ARE AVERAGE EXPECTED VALUES BASED UPON RATED VOLTAGE, FREQUENCY AND SINEWAVE POWER INPUT.

\* TEMPERATURE RISE WILL BE CONSISTENT WITH INSULATION, AMBIENT AND SERVICE FACTOR AS DEFINED BY NEMA-MG-12.43 OR -20.40.

\*\* BEARINGS ARE THE ONLY RECOMMENDED SPARE PART(S).

**CERTIFIED BY:**  
**DATE:**

**TOSHIBA**

Reliability in Motion

**TOSHIBA INTERNATIONAL CORPORATION**

INDUSTRIAL DIVISION

PO BOX 40906

HOUSTON TX 77240

(713) 466-0277

(800) 231-1412

FAX (713) 466-8773

**SPARE PARTS (RECOMMENDED)**

OTHER THAN THE GREASE USED FOR RE-GREASABLE BEARINGS, **TOSHIBA** ADVISES THAT THERE ARE NO "USE" PARTS. THE ONLY INSURANCE SPARES THAT **TOSHIBA** SUGGESTS FOR THESE SQUIRREL CAGE INDUCTION MOTORS ARE INDUSTRY STANDARD, AND COMMERCIALY AVAILABLE ANTI-FRICTION BEARINGS, AS NOTED BELOW.

MOTOR COMPONENTS (SUCH AS TERMINAL BOXES, FAN COVERS, MACHINED PARTS) ARE AVAILABLE UPON SPECIAL REQUEST. IN THIS CASE, PLEASE ADVISE OUR ORDER ENTRY DEPARTMENT THE MODEL AND SERIAL NUMBERS (FOUND ON THE MOTOR NAMEPLATE) , AND A DESCRIPTION OF THE COMPONENT REQUIRED. THEY WILL THEN FURNISH THE CURRENT PART NUMBER, PRICE AND AVAILABILITY.

(NOTE: OUR INTERNAL PART NUMBERS ARE SUBJECT TO CHANGE WITHOUT NOTICE, AND ARE NOT PUBLISHED).

PLEASE ADVISE IF YOU HAVE ANY QUESTIONS.

CUSTOMER:  
PURCHASE ORDER #  
Customer Tag:

TOSHIBA FILE #  
MODEL # 0602DPSC31B-P  
HP / RPM / ENCL / FRAME: 60 / 3600 / ODP / 326TS  
DRIVE END BEARING: 6312C3  
OPPOSITE DRIVE END BEARING: 6212C3

**Prepared By:**  
**Date:**