



TECHNICAL INFORMATION

- BEARING LUBRICATION DE: Mobil Polyrex EM
ODE: Mobil Polyrex EM
- BEARING TYPE DE: 6315C3
ODE: 6315C3 INSULATED
- WINDING TEMP. DETECTORS
NUMBER AND TYPE: 6xRTD(Pt0°C-100ohm)
LOCATION: IN STATOR SLOT
- BEARING TEMP. DETECTORS
NUMBER AND TYPE: _____
- SPACE HEATER 1 PHASE
VOLTS: 120 WATTS: 400
- ROTATION: CCW VIEWED FROM NON DRIVE END
THIS MOTOR IS UNI DIRECTIONAL
- MOTOR PAINT COLOR: _____
- APPROX. WEIGHT: 7300 Lbs
- ACCESSORIES: _____

DRAWING LIST					
MAIN TERMINAL BOX	3	UPDATE	RWS	1/2/14	
130-7532-02					
AUX TERMINAL BOX FOR	2	UPDATE	MH	8/15/05	
SPACE HEATER 130-7520-50					
R.T.D. 130-7522-51	1	UPDATE	RW	4/16/03	
THERMISTOR N/A					
	0	FIRST ISSUE	RW	3/25/03	
PRODUCTION #	N/A	NO.	REVISION	BY	DATE

MOTOR OUTLINE FOR
THREE PHASE INDUCTION MOTOR

CUSTOMER NAME				P.O. NO.	MOTOR TAG NO.	
OUTPUT	POLE	VOLTAGE	FREQUENCY	FULL LOAD SPEED	TOSHIBA MODEL NO.	
HP	2	V	Hz	(min ⁻¹)		
TYPE	FORM	INS. CLASS	RATING	FRAME	S.F.	ENCLOSURE
		F	CONT.	5811/12		WP-I
TOSHIBA INTERNATIONAL CORPORATION HOUSTON, TEXAS U.S.A.						
3rd ANGLE PROJ.	PREPARED BY:	DATE:	CHECKED BY:	DATE:	DRAWING NO.:	REV.:
	R. WILKINS	03/25/03	M. HO	04/01/03	MDSL 0086-01	3