



**TECHNICAL INFORMATION**

1. BEARING LUBRICATION DE: MOBIL POLYREX EM  
ODE: MOBIL POLYREX EM
2. BEARING TYPE DE: 6315C3  
ODE: 6315C3 INSULATED
3. WINDING TEMP. DETECTORS  
NUMBER AND TYPE: 6xRTD(PtO°C-100ohm)  
LOCATION: IN STATOR SLOT
4. BEARING TEMP. DETECTORS  
NUMBER AND TYPE: \_\_\_\_\_
5. SPACE HEATER 1 PHASE  
VOLTS: 120 WATTS: 400
6. ROTATION: CCW VIEWED FROM NON DRIVE END  
THIS MOTOR IS UNI DIRECTIONAL
7. MOTOR PAINT COLOR: \_\_\_\_\_
8. APPROX. WEIGHT: 7300 Lbs
9. ACCESSORIES: \_\_\_\_\_

**PRELIMINARY DRAWING ONLY  
(DO NOT BUILD)**

DRAWING LIST				
MAIN TERMINAL BOX 130-7532-02	3	BA FROM 8" PER MARKETING/A.E. (RM)	MCA	01/19/17
AUX TERMINAL BOX FOR SPACE HEATER	2	CORRECT JACKING HOLE LOCATION FROM 1.7"	ED	2/24/14
R.T.D.	1	JACKING TO INLINE	RWS	1/3/14
THERMISTOR	0	FIRST ISSUE	BCS	12/4/13
PRODUCTION #	N/A	NO.	REVISION	BY DATE

MOTOR OUTLINE FOR THREE PHASE INDUCTION MOTOR						
CUSTOMER NAME			P.O. NO.		MOTOR TAG NO.	
OUTPUT HP	POLE	VOLTAGE V	FREQUENCY Hz	FULL LOAD SPEED (min <sup>-1</sup> )	TOSHIBA MODEL NO.	
TYPE	FORM	INS. CLASS F	RATING CONT.	FRAME 5809/10/11	S.F.	ENCLOSURE WP-II
TOSHIBA INTERNATIONAL CORPORATION HOUSTON, TEXAS U.S.A.						
3rd ANGLE PROJ.	PREPARED BY: B SIDLE	DATE: 12/4/13	CHECKED BY: ED R.	DATE: 12/31/13	DRAWING NO.: MDSL0087-101	REV. 3

UNITS: INCHES

