

NOTES:

- 1. MAIN CONDUIT BOX MAY BE ROTATED
- IN 90~INCREMENTS

 2. STANDARD PRODUCT USE BI-DIRECTIONAL FAN. OPPOSITE ROTATION AVAILABLE
- ONLY BY CONNECTION CHANGE.

 3. KEY DIMENSIONS EQUAL 0.625"x0.625"x4.28" (MOTOR SUPPLIED WITH KEY)

UNITS: mm [INCHES] TOSHIBA RESERVES THE RIGHT TO MAKE CHANGES OF TECHNICAL IMPROVEMENT WITHOUT NOTICE. DO NOT USE FOR CONSTRUCTION, INSTALLATION, OR APPLICATION PURPOSES UNLESS THE DRAWING IS CERTIFIED. **TOLERANCES** 360T TEFC FRAME .X .1 Tosh-ECO OWP F2 ASSEMBLY .XX .03 XXX. .005 .0005 XXXX. MDSLE021-10 MAXIMUM MOTOR WEIGHT DRAWN BY: Lin Qingliu CHECK BY: Cai Zhengiang lbs. APPROVED BY: Li Zhuoqing FIRST ISSUE Lin Qingliu 03/15/17 kgs. TOSHIBA INTERNATIONAL CORPORATION NO REVISION DRAWN BY DATE CHECK www.toshiba.com/ind

TOSHIBA

Issued Date	10/31/2016	Transmit #	
Issued By	Huang Zhenxiong	Issued Rev	0

TYPICAL MOTOR PERFORMANCE DATA

Model: <u>OW2</u>0

HP	kW	Pole	FL RPM	Frame	Voltage	Hz	Phase	FL Amps
40	30	6	1108	364T	230/460	60	3	100/50
Enclosure	IP	Ins. Class	S.F.	Duty	NEMA Nom. Eff.	NEMA Design	kVA Code	Ambient (°C)
TEFC	55	F	1.15	CONT	-	D	G	40

Load	HP	kW	Amperes(460)	Efficiency (%)	Power Factor (%)
Full Load	40	29.83	50.2	87.1	85.7
¾ Load	30.00	22.37	38.5	89.0	82.0
½ Load	20.00	14.91	28.8	89.0	73.0
1/4 Load	10.00	7.46	21.3	86.0	51.0
No Load			17.2		6.6
Locked Rotor			285		45.9

Torque						
Full Load Locked Rotor Pull Up Break Down						
(lb-ft)	(% FLT)	(% FLT)	(% FLT)	(lb-ft²)		
191	288	296	304	23.1		

Safe Stall	Time(s)	Sound	Bearings*		Approx. Motor Weight
Cold	Hot	Pressure	Bearii	Approx. Motor Weight	
Colu	dB(A) @ 1M		DE	NDE	(lbs)
29	13	69	6314/C3	6314/C3	838

*Bearings are the only recommended spare part(s).

Motor	Op	tions:
-------	----	--------

Customer	
Customer PO	
Sales Order	
Project #	

Tag:

All characteristics are average expected values. The declared locked rotor current has a tolerance of 20%.

TOSHIBA INTERNATIONAL CORPORATION · HOUSTON, TEXAS U.S.A.								
Engineering		Doc. Written By	P. Anderson	Doc.# / Rev	MDSLE021-10/0			
Engr. Date		Doc. Approved By	PAA	Doc. Issued	10/31/2016			



Issued Date 10/31/2016	Transmit #
Issued By Huang Zhenxiong	Issued Rev 0


SPEED TORQUE/CURRENT CURVE

Model: OW20

HP	kW	Pole	FL RPM	Frame	Voltage	Hz	Phase	FL Amps
40	30.0	6	1108	364T	230/460	60	3	100/50
Enclosure	IP	Ins. Class	S.F.	Duty	NEMA Nom. Eff.	NEMA Design	kVA Code	Ambient (°C)
TEFC	55	F	1.15	CONT	=	D	G	40
Locked Rotor	Rotor wk ²			To	orque			
Amps	Inertia	Full Load Ib-ft	Locked	Rotor	Pull Up		Break	Down
Allips	(lb-ft²)	(lb-ft)	(%	.)	(%)		(%	%)
285	23.1	191	288	8	296		30	04

CHARACTERISTIC CURVES RELATED TO SPEED

Three-phase induction motor-Squirrel cage rotor



Customer	wk² Load Inertia (Ib-ft²)	-
Customer PO	Load Type	-
Sales Order	Voltage (%)	100
Project #	Accel. Time	-

Tag:

All characteristics are average expected values.

TOSHIBA INTERNATIONAL CORPORATION · HOUSTON, TEXAS U.S.A.								
Engineering Doc. Written By P. Anderson Doc.# / Rev MI								
Engr. Date		Doc. Approved By	PAA	Doc. Issued	10/31/2016			

TOSHIBA

Issued Date	10/31/2016	Transmit #	
Issued By	Huang Zhenxiong	Issued Rev	0

NAMEPLATE DATA

Model: OW20

Comments 4:

HP	kW	Pole	FL RPM	Frame	Voltage	Hz	Phase	FL Amps
40	30.0	6	1108	364T	230/460	60	3	100/50
Enclosure	IP	Ins. Class	S.F.	Duty	NEMA Nom. Eff.	NEMA Design	kVA Code	Ambient (°C)
TEFC	55	F	1.15	CONT	-	D	G	40

Customer	
Customer PO	
Sales Order	
Project #	

Tag:

All characteristics are average expected values.

TOSHIBA INTERNATIONAL CORPORATION · HOUSTON, TEXAS U.S.A.							
Engineering		Doc. Written By	P. Anderson	Doc.# / Rev	MDSLE021-10/0		
Engr. Date		Doc. Approved By	PAA	Doc. Issued	10/31/2016		



Issued Date	10/31/2016	Transmit #	
Issued By	Huang Zhenxiong	Issued Rev	0

SPARE PARTS LIST*

Model: OW20

HP	kW	Pole	FL RPM	Frame	Voltage	Hz	Phase	FL Amps
40	30.0	6	1108	364T	230/460	60	3	100/50
Enclosure	IP	Ins. Class	S.F.	Duty	NEMA Nom. Eff.	NEMA Design	kVA Code	Ambient (°C)
TEFC	55	F	1.15	CONT	-	D	G	40

Bearings DE	6314/C3
Bearings NDE	6314/C3

*Bearings are the only recommended spare part(s).

Other than the grease used for regreasable bearings and the oil used for oil-lubricated bearings, Toshiba advises that there are no "use" parts. The only insurance spares that Toshiba suggests for these squirrel-cage induction motors are industry-standard and commercially available off-the-shelf bearings as noted above.

Motor components such as terminal boxes, fan covers and other machined parts are available on special request. In these cases, please advise our order entry department of the model and serial numbers found on the motor nameplate and a description of the needed components. With this information they will be able to furnish the current part number, price and availability.

Note: Our internal part numbers are subject to change without notice and are not published.

Customer	
Customer PO	
Sales Order	
Project #	

Tag:

All characteristics are average expected values.


TOSHIBA INTERNATIONAL CORPORATION · HOUSTON, TEXAS U.S.A.							
Engineering Doc. Written By P. Anderson Doc.# / Rev MDSLE021-10							
Engr. Date		Doc. Approved By	PAA	Doc. Issued	10/31/2016		




Motor Connection Diagrams 12 Leads Dual Voltage


Across-the-Line Starting / Running Connections


Low Voltage Delta





High Voltage Delta







Switch L1 and L2 to reverse rotation

By: R. Murillo Date: 4/9/08 Checked: Date: Revision 0