

NOTES:

- 1. MAIN CONDUIT BOX MAY BE ROTATED IN 90° INCREMENTS
- 2. STANDARD PRODUCT USES BI-DIRECTIONAL FAN. OPPOSITE ROTATION AVAILABLE ONLY BY CONNECTION CHANGE.
- 3. KEY DIMENSIONS EQUAL

0.375"x 0.375"x 2.88"

(MOTOR SUPPLIED WITH KEY)

TOSHIBA RESERVES THE RIGHT TO MAKE CHANGES OF TECHNICAL IMPROVEMENT AND THE DATA MAY CHANGE WITHOUT NOTICE

PRELIMINARY

DO NOT USE FOR CONSTRUCTION, INSTALLATION, OR APPLICATION PURPOSES UNLESS THE DRAWING IS MARKED AS CERTIFIED

X CERTIFIED



TOTALLY ENCLOSED FAN COOLED HORIZONTAL FOOT MOUNTED 3 PHASE INDUCTION MOTOR F1 ASSEMBLY 254T-256T

DRAWING #: MDSLV081-04 REV. DATE: 06/30/18

REV. #: 0 PER.: M. O'DOWD

REV. DESCRIP.:



Issued Date	7/19/2021	Transmit #	
Issued By	dschoeck	Issued Rev	

TYPICAL MOTOR PERFORMANCE DATA

Model: 0058XDSC41A-P

HP	kW	Pole	FL RPM	Frame	Voltage	Hz	Phase	FL Amps
5	3.7	8	870	254T	575	60	3	6.0
Enclosure	IP	Ins. Class	S.F.	Duty	NEMA Nom. Eff.	NEMA Design	kVA Code	Ambient (°C)
TEFC	56	F	1.15	CONT	86.5	В		40 C

Load	HP	kW	Amperes	Efficiency (%)	Power Factor (%)
ull Load	5.00	3.7	6.0	88.1	70.6
4 Load	3.75	2.8	5.0	87.8	63.7
∕₂ Load	2.50	1.9	4.2	85.6	51.7
4 Load	1.25	0.9	3.7	77.0	32.5
lo Load			3.1		5.3
ocked Rotor			28		38.9

Torque							
Full Load	Full Load Locked Rotor Pull Up Break Down						
(lb-ft)	(% FLT)	(% FLT)	(% FLT)	(lb-ft²)			
30.2	185	145	225	2.10			

Safe Stall Time(s)		Sound	Bearin	Approx. Motor Weight		
Cold	Hot	Pressure	Bearings*		Approx. Motor Weight	
Colu	dB(A) @ 1I		DE	NDE	(lbs)	
35	15	-	6309C3	6309C3		

*Bearings are the only recommended spare part(s).

Motor Options: Mounting:Footed,Shaft:T Shaft

Customer	
Customer PO	
Sales Order	
Project #	

Tag:

All characteristics are average expected values.

TOSHIBA INTERNATIONAL CORPORATION · HOUSTON, TEXAS U.S.A.							
Engineering	aguerrettaz Doc. Written By D. Suarez Doc.# / Rev Mi						
Engr. Date	4/5/2019	Doc. Approved By	M. Campbell	Doc. Issued	6/8/2011		




Issued Date	7/19/2021	Transmit #	
Issued By	dschoeck	Issued Rev	

SPEED TORQUE/CURRENT CURVE

Model: 0058XDSC41A-P

HP	kW	Pole	FL RPM	Frame	Voltage	Hz	Phase	FL Amps
5	3.7	8	870	254T	575	60	3	6.0
Enclosure	IP	Ins. Class	S.F.	Duty	NEMA Nom. Eff.	NEMA Design	kVA Code	Ambient (°C)
TEFC	56	F	1.15	CONT	86.5	В		40 C
Lealind Dates	Rotor wk ²	Torque						
Locked Rotor Amps	Inertia	Full Load	Locked	Rotor	Pull Up)	Break	Down
	(lb-ft²)	(lb-ft)	(%	5)	(%)		(%	%)
28	2.10	30.2	185		145		22	25

Design Values






Customer	wk² Load Inertia (lb-ft	-				
Customer PO	Load Typ	е -				
Sales Order	Voltage (%	100				
Project #	Accel. Tim	e -				


Tag:

All characteristics are average expected values.

TOSHIBA INTERNATIONAL CORPORATION · HOUSTON, TEXAS U.S.A.							
Engineering	Engineering aguerrettaz Doc. Written By D. Suarez Doc.# / Rev MPCF-11.						
Engr. Date	4/5/2019	Doc. Approved By	M. Campbell	Doc. Issued	6/8/2011		

Motor Connection Diagram 3 Leads - Delta Connection





Switch L1 and L2 to reverse rotation

Each lead may consist of more than one cable. If multiple cables represent a single lead, each one of them will be labeled with the appropriate lead number.

By: R. Murillo Date: 4/9/08 Checked: MDC Date: 5/17/11 Revision 0